

Radial Multilayer Ceramic Capacitors

multicomp PRO




**RoHS
Compliant**

Feature

- Miniature size and large capacitance
- Tape and reel packaging suitable for auto-placement
- Epoxy resin coating creates excellent performance in humidity resistance, mechanical strength and heat resistance

Size Code and Voltage VS Capacitance



Size Code	Shape	Dimensions				
		F ±0.5	H min.	L max.	W max.	T max.
0805	C1	5.08mm	10mm	4.2mm	3.8mm	3mm

Size Code	Shape	Voltage	Available Capacitance Range
			X7R
0805	C1	50V	334

Reliability and Test Method for General Ledged MLCC

Item	Technical Specification		Test Method and Remarks		
Capacitance (C)	Class I	Within the specified tolerance.	Capacitance	Measuring Frequency	Measuring Voltage
			≤1000pF	1MHz ±10%	1 ±0.2V
	>1000 pF	1kHz ±10%			
	Class II	Within the specified tolerance.	The capacitance should be pretreated before measured(only for class II).		
Measuring Frequency			Measuring Voltage		
1kHz ±10%			B: 1 ±0.2V		
Dissipation Factor (DF)	Class I	$C_R \geq 50\text{pF}$ $DF \leq 0.15\%$ $C_R < 50\text{pF}$ $DF \leq 1.5 [(150/C_R) + 7] \times 10^{-4}$	Capacitance	Measuring Frequency	1 ±0.2V
			≤1000pF	1MHz ±10%	
			>1000 pF	1kHz ±10%	
	Class II	B	DF ≤3.5%	1kHz ±10%; Measuring Frequency: 1kHz ±10% 1 ±0.2V Measuring Voltage: 1kHz ±10%	
Insulation Resistance	Class I	$C \leq 10\text{nF}$ $IR \geq 10000\text{M}\Omega$ $C > 10\text{nF}$ $R.C \geq 100\text{QF}$	Measuring Voltage: Rated Voltage Duration: 60±5s		
	Class II	$C \leq 25\text{nF}$ $IR \geq 4000\text{M}\Omega$ $C > 25\text{nF}$ $R.C \geq 100\text{QF}$			

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Radial Multilayer Ceramic Capacitors

multicomp PRO


Item	Technical Specification	Test Method and Remarks	
Withstanding Voltage	No breakdown or damage.	Between terminals: Measuring Voltage: Duration: 5±1s Class I : 300% Rated voltage Class II : 250% Rated voltage The charge/discharge current is less than 50mA.	
		Between terminals and body Voltage: 2.5 times rated voltage Duration:1~5s Small metallic ball method Small metallic balls with 1mm diameters shall be put in a vessel and the test capacitor shall be submerged except 2mm from the top of its component body and the terminals. The test voltage shall be applied between the short-circuited terminals and the metallic balls.	
Solder ability	Lead wire shall be at least 75% covered with a new solder coating.	The terminal of capacitor is dipping into a 25% rosin solution of ethanol and then into molten solder (Sn-2.5Ag-1Bi-0.5Cu) of 245 ±2°C for less than 3s. In both cases the depth of dipping is up to about 1.5~2mm from the terminal body.	
Resistance to Soldering Heat	Item	$\Delta C/C \leq$	
	Class I	$\pm 2.5\%$ or $\pm 0.25\text{pF}$	
	B	$\pm 10\%$	
	No significant abnormality in appearance.		Solder temperature: 265 ±3°C Duration: 6 (+1,0)s Immersed conditions: Inserted into the PC board (with t=1.6mm, hole=1.0mm diameter) Recovery: For class I, 4 to 24 hours of recovery under the standard condition after test. Preconditioning (Class II): 1 hour of preconditioning at 150(-10,+0)°C, followed by 48 ±4 hours of recovery under the standard condition. Recovery (Class II) : 48 ±4 hours of recovery under the standard condition after test.
High Temperature Loading Test	No significant abnormality in appearance.		Temperature
	Capacitance Change: Class I: $\leq \pm 3\%$ or $\pm 0.3\text{pF}$ Whichever is larger. Class II: B: $\leq \pm 12.5\%$		X7R
	Dissipation Factor: Class I: Not more than twice of initial value. B: $\leq 5\%$		125(-0,+3)°C
	Insulation Resistance: $\geq 500\text{M}\Omega$ or $25\Omega.F$ Whichever is smaller.		Applied voltage: 1.5 times rated voltage The charge/ discharge current is less than 50mA. Duration: 1000 (-0, +48) hours Recovery Time: Class I Dielectric: 24 ±2 hours Class II Dielectric: 48 ±4 hours
Solvent Resistance	No defects or abnormalities in appearance and legible marking.	Solvent temperature: put the sample into solvent 1 Min, and then take it out and brush sample's notation area 10 times with pledged, repeat 3 times.	

*Note on standard condition: "standard condition" referred to herein should be defined as follows:
5 to 35°C of temperature, 45 to 75% of relative humidity, and 86 to 106kPa of atmospheric pressure.

Radial Multilayer Ceramic Capacitors



Packaging Style



Code	P0	P	P1	P2	d	Δh	W	W0	W1	W2	H	H0	D	t
Dim.	12.7	12.7	3.85 5.1	6.35	0.5	0	18.5	12	9	1.5	32.25	15~20	4	0.7
Tol.	±0.2	±0.2	0.7	±1.3	±0.1	±2	±1	±1	±0.5	±1.5	Max.	±0.5	±0.2	Max.

P1=3.85mm for F=5.08mm; P1=5.1mm for F=2.54mm

Part Number Table

Description	Part Number
Capacitor, MLCC, X7R, 0.33μF, 50V, ± 10%, 5.08mm, 0805	MC0805B334K500A5.08MM

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

