Standard MOV Varistor Zinc Oxide, 10mm

multicomp PRO




Materials:

Ceramic Disk Electrode Material Coating Material Lead Material

- : Zinc Oxide Varistor
- : Ag Paste
- : Epoxy Resin
- : Tin Plated Copper Wire

Electrical Rating:

Varistor Voltage	Min	387 Volts
	Max	473 Volts
Maximum Allowable Voltage	AC rms	275 Volts
	DC	370 Volts
Maximum Clamping Voltage at 25A, 8/20µs		710 Volts
Withstanding Surge Current, 8/20µs		2500 A
Rated Transient Power Dissipation		0.4 W
Maximum Energy (10/1000µs)		65 Joules
Maximum Energy (2mS)		45 Joules
Typical Capacitance at 1kHz		310 pF



Dimensions : Millimetres

Dimensions:

_		
	Dmax	14mm
	Tmax	5mm
ĺ	d±0.02	0.8mm
ĺ	W	7.5±1mm
ſ	Hmax	17mm
	L(min)	25mm

Part Number Table

Description	Part Number
Varistor, 65J, 275Vrms	MCSR431K10DS

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

