



Shielded Cable Assemblies

EMI Pigtails



MIL-STD-83513 Cable Assemblies

Cinch DURA-CON D-shaped micro miniature rectangular connectors are designed for applications that require a rugged, high performance, densely compacted interconnect. DURA-CON is the ideal connector for applications where weight and space must be kept to a minimum while maintaining maximum reliability.

Reliability is assured with the unique twist pin providing 7 points of contact when mated. Qualified (QPL) to MIL-DTL-83513, micro-D DURA-CON are one of the most widely used 0.05in (1.27mm) pitch connectors. Typical applications for these connectors are miniaturized military and aerospace electronics and data processing equipment, where shorter signal paths are needed

Features

- MIL-DTL-83513
- 78 ohm twinax cable
- 50 and 75 ohm triax cable
- 50 and 75 ohm triax cable

Materials

Connector Shell

ASTM Alloy< SAE-AMS-QQ-A-250. Cadmium per SAE-AMS-QQ-P-416. Electroless Nickel per SAE-AMS-C-26074. Gold per MIL-G-45204

Contact (Male Pins)

Copper Alloy. Gold per MIL-DTL-45204, Type 1

Contact (Female Sockets)

Copper Alloy. Gold per MIL-DTL-45204, Type 1

Insulator

PBT< per MIL-M-24519 or >DAP< PER ASTM-D5948

Hardware

303SS< Passivate Dip per SAE-AMS-QQ-P-35

Interfacial Gasket

FVMQ< per MIL-R-25988 or >PMQ< PER ZZ-R-765

Dustcap

LDPE< or anti-static >HDPE<

Wire

See sales code nomenclature

Electrical

Current Rating

3 AMP MAX

Temperature Rating

-55 °C TO +135 °C

Insulation Resistance

5000 mΩ min

DWV at Seal Level

600 Vac

DWV 70,000 feet Altitude Contact Resistance


150 Vac 8 mO max






Dura-Con™


Socket Connector



Plug Connector



Hardware







Ordering Information

