

Automotive Grade, 4 Pad 2.0mm x 1.6mm SMD, LVCMOS Oscillator, 32.768kHz

Product Features:

- AEC-Q200 qualified
- IATF 16949 certified production lines
- LVCMOS compatible output
- Low 50µA Input Current
- AT Cut Temperature Stability Characteristic
- Six supply voltages options, 1.8V, 2.5V, 2.8V, 3.0V, 3.3V, 1.62V to 3.63V (Continuous)
- RoHS and REACH compliant

ELECTRICAL SPECIFICATIONS

Typical Applications:

- Real Time Clock
- Infotainment System
- Instrument Panel, Ethernet
- ADAS, Camera, Video
- LIDAR Systems, Navigation
- Engine Control Units

Frequency Range	32.768kHz				
Frequency Stability	±25ppm Maximum ±50ppm Maximum ±100ppm Maximum	Inclusive of Initial Tolerance, Stability over Operating Temperature Range, Load (±5%), Voltage (±5%), and Aging (First Year at +25°C)			
Operating Temperature Range	-40°C to +85°C -40°C to +105°C -40°C to +125°C				
Supply Voltage (Vdd)	1.8V, 2.5V, 2.8V, 3.0V, 3.3V, or 1.62V to 3.63V				
Input Current	50µA Typical, 100µA Maximum	No Load, Vdd = 3.3V			
Output Logic Type	LVCMOS				
Output Drive Capability	15pF Maximum				
Aging	±3ppm/year Maximum	at +25°C			
Duty Cycle	50 ±5(%)	Measured at 50% of waveform			
Rise / Fall Time	15nSec Maximum	Measured from 10% to 90% of waveform			
Output Voltage Logic High	90% of Vdd Minimum				
Output Voltage Logic Low	10% of Vdd Maximum				
Input Voltage Logic High	70% of Vdd Minimum or No Connect to Enable Output				
Input Voltage Logic Low	30% of Vdd Maximum to Disable Output (High Impedance)				
Standby Current	1μΑ Typical, 3μΑ Maximum	Disabled Output, High Impedance			
Startup Time	2mSec Maximum				
 All minimum and maximum limits are specified over temperature and rated operating voltage with 15pF output unless otherwise stated. A 0.1µF bypass capacitor is recommended between Vdd (pad 4) and GND (pad 2) to minimize power supply noise. 					

ABSOLUTE MAXIMUM LIMITS

Storage Temperature Range	-55°C to +125°C		
Supply Voltage Range	-0.3Vdc to Vdd +0.5Vdc		
Electrostatic Discharge	2000V Maximum		
Solder Temperature	260°C Maximum		
Junction Temperature	150°C Maximum		
NOTE: If the part is used beyond absolute maximum ratings, it may cause internal destruction. The part should be used under the recommended			

NOTE: If the part is used beyond absolute maximum ratings, it may cause internal destruction. The part should be used under the recommend operating conditions or the reliability of this part may be damaged if those conditions are exceeded.

PART	PART NUMBER GUIDE						
Series	Supply Voltage	Operating Temperature Range	Frequency Stability	Function	Frequency		
IKA11-	1 = 1.8V 6 = 2.5V 2 = 2.8V 7 = 3.0V 3 = 3.3V 8 = 1.62V to 3.63V	2 = -40°C to +85°C E = -40°C to +105°C F = -40°C to +125°C	A = ±25ppm * B = ±50ppm ** C = ±100ppm	H = Output Enable	-32.768 kHz		
Sample	Sample Part Number: IKA11-8FCH-32.768 kHz						
NOTES:	 NOTES: * Only available with Operating Temperature Range option 2. ** Only available with Operating Temperature Range option 2 and E. Please consult with Sales Department any other parameters or options. 						








Automotive Grade, 4 Pad 2.0mm x 1.6mm SMD, LVCMOS Oscillator, 32.768kHz

IKA11 Series


MECHANICAL & SOLDER PAD LAYOUT DIMENSIONS




MARKING PACKAGE INFORMATION Line 1: 32.768K Termination = e4 (Au over Ni over W base metallization Line 2: Date Code (YWW) Terminal Plating Thickness: Gold (0.3µm to 1.0µm), Nickel (1.27µm to 8.89µm)

ENVIRONMENTAL SPECIFICATIONS		
Mechanical Shock	MIL-STD-202, Method 213	
Mechanical Vibration	MIL-STD-202, Method 204	
Resistance to Soldering Heat	MIL-STD-202, Method 210	
Solderability	J-STD-002	
Gross Leak	MIL-STD-883, Method 1014	
Fine Leak	MIL-STD-883, Method 1014	
Moisture Sensitivity Level	MSL 1 (+260°C)	

TAPE & REEL DIMENSIONS






QUALITY SYSTEM CERTIFIED = ISO 9001 = ILSI America Phone 775-851-8880 • Fax 775-851-8882 •email: e-mail@ilsiamerica.com • www.ilsiamerica.com Specifications subject to change without notice Rev: 06/14/19_A






Automotive Grade, 4 Pad 2.0mm x 1.6mm SMD, LVCMOS Oscillator, 32.768kHz

IKA11 Series





PROPRIETARY AND CONFIDENTIAL

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION, AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE NOR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM ILSI America.

QUALITY SYSTEM CERTIFIED = ISO 9001 = Rev: 06/14/19_A