

Special function module - EEM-IMP-MA600 - 2904313


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Function module with two pulse outputs for the EEM-MA600



RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 804257
GTIN	4046356804257
Weight per Piece (excluding packing)	128.000 g
Custom tariff number	90309000
Country of origin	Hungary
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	22.5 mm
Height	65 mm
Depth	48 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C (14 °F to 131 °F)
Ambient temperature (storage/transport)	-20 °C ... 85 °C (-4 °F ... 185 °F)
Max. permissible relative humidity (operation)	≤ 95 %
Max. salt spray content	≤ 2.5 %

Output data

Output description	Relay output
Number	2
Maximum switching voltage	100 V DC
Switching capacity	10 VA (0.5 A)

Special function module - EEM-IMP-MA600 - 2904313

Technical data

Interfaces

Connection method	Pluggable screw terminal block
-------------------	--------------------------------

General

Supply voltage	9 V (via EEM-MA600)
Color	black
Conformance	CE-compliant
Rated insulation voltage	300 V AC (EN 61010-1)
Test voltage	3.5 kV AC (50 Hz, 1 min.)
	2.2 kV AC (50 Hz, 1 min.)

Standards and Regulations

Conformance	CE-compliant
UL, USA/Canada	UL 61010-1
	CSA-C22.2 No. 61010-1
	cULus

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27371800
eCl@ss 5.1	27371800
eCl@ss 6.0	27149200
eCl@ss 7.0	27149223
eCl@ss 8.0	27149223
eCl@ss 9.0	27142336

ETIM

ETIM 4.0	EC002295
ETIM 5.0	EC002295
ETIM 6.0	EC002295
ETIM 7.0	EC002295

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535

Special function module - EEM-IMP-MA600 - 2904313

Classifications

UNSPSC

UNSPSC 13.2	32151602
UNSPSC 19.0	32151602