



# 196 HVC ENYCAP™ HYBRID ENERGY STORAGE CAPACITORS



Electrostatic Storage

+





Electrochemical Storage

=




Hybrid Storage

## THE 196 HVC ENYCAP "SWEET SPOT"



## 196 HVC ENYCAP POWER SOURCE



## STACKABLE




## Higher Energy Density by Volume



## 460 Ws OF STORED ENERGY (4 CELLS)

Example 1 A for 200 s



## 196 HVC ENYCAP vs. a Battery

- More charge and discharge cycles: over 100 000
- No memory effect
- Longer lifetime

## 196 HVC ENYCAP vs. a Traditional Supercapacitor

- Lower self-discharge
- More than 3 times the energy density
- No cell balancing

## 4 CAPACITANCE OPTIONS



Not just a capacitor, it's the 196 HVC ENYCAP hybrid energy storage capacitor!

[hybridstorage@vishay.com](mailto:hybridstorage@vishay.com)