

18V MULTI TOOL LXT

DTM51Z

Models DTM51 have been developed based on models BTM50 and equipped with the tool-less accessory change system.

18V MULTI TOOL LXT



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Shank	OIS
Oscillation Angle	3.2 °
Oscillations per Minute	6,000 - 20,000
Maximum Output	390 w
Vibration K factor	1.5 m/sec ²
Vibration: Sanding	3.0 m/sec ²
Vibration: Scraping	5.5 m/sec ²
Vibration: Plunge Saw Blade	7.0 m/sec ²
Vibration: Segmental Saw Blade	4.5 m/sec ²
Net weight	2.0 - 2.4 kg

USER BENEFITS

- Tool-less accessory clamp. Lever style lock system allows for quick installation and replacement of accessories,.
- Ergonomically best possible barrel grip, with a perfect circumference size and shape which fits the hand for extra comfortable handling.
- Battery capacity warning lamp Blinking red; Battery power has been nearly used up. Solid red; Battery power has been used up (Battery protector will shut off the power.)
- Accessories can be installed at 30° increments, across 360°
- Variable speed control dial.
- Soft start
- Anti-restart function.
- High operating efficiency.

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER