

305mm Slide Compound Mitre Saw

LS1219

305mm Slide Compound Mitre Saw. Motor head slides on fixed pipes without extending to the rear of the machine, allowing the machine to be placed close to the wall.



TECHNICAL SPECIFICATIONS

Blade Diameter	305 mm
Max mitre range	60 - 60 °
Max mitre cut at 90°	92 x 382 mm
Bore Diameter	30 mm
Max bevel range	48 - 48 °
Noise sound pressure	91 dB(A)
Noise sound power	100 dB(A)
Noise K factor	3 dB(A)
Input Wattage 110v	1,450 w
Input Wattage 240v	1,800 w
No Load Speed	3200 rpm
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	29.3 kg

USER BENEFITS

- Motor head slides on fixed pipes without extending machine at rear end, so the machine can be placed close to wall.
- Front knob for easy bevel adjustment
- Holders to support a wide workpiece
- Easy-to-operate mitre angle lock
- One-touch sliding lock
- Large turn base
- Connects to dust extractor
- Electric brake
- Soft start
- Constant speed control
- Double Insulation

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER