# Product datasheet Characteristics

## CAD50MD

TeSys D control relay - 5 NO - <= 690 V - 220 V DC standard coil





#### Main

Range	TeSys
Product name	TeSys CAD
Product or component type	Control relay
Device short name	CAD
Contactor application	Control circuit

#### Complementary

DC-13	
AC-14	
5 NO	
<= 690 V AC 25400 Hz	
DC standard	
220 V DC	
6 kV conforming to IEC 60947	
10 A (at 60 °C)	
140 A AC conforming to IEC 60947-5-1	
250 A DC conforming to IEC 60947-5-1	
100 A - 1 s	
140 A - 100 ms	
10 A gG conforming to IEC 60947-5-1	
600 V UL certified	
600 V CSA certified	
690 V conforming to IEC 60947-5-1	
Rail	
Plate	
Screw clamp terminals 1 cable(s) 14 mm²flexible without cable end	
Screw clamp terminals 2 cable(s) 14 mm²flexible without cable end	
	AC-15 AC-14  5 NO  <= 690 V AC 25400 Hz  DC standard  220 V DC  6 kV conforming to IEC 60947  10 A (at 60 °C)  140 A AC conforming to IEC 60947-5-1  250 A DC conforming to IEC 60947-5-1  100 A - 1 s  120 A - 500 ms  140 A - 100 ms  10 A gG conforming to IEC 60947-5-1  600 V UL certified 600 V CSA certified 690 V conforming to IEC 60947-5-1  Rail Plate  Screw clamp terminals 1 cable(s) 14 mm²flexible without cable end

	Screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Screw clamp terminals 1 cable(s) 14 mm²solid without cable end Screw clamp terminals 2 cable(s) 14 mm²solid without cable end
Tightening torque	1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
Control circuit voltage limits	Operational: 0.71.25 Uc Drop-out: 0.10.25 Uc
Operating time	5372 ms coil energisation and NO closing 1624 ms coil de-energisation and NO opening
Mechanical durability	30 Mcycles
Maximum operating rate	180 cyc/mn
Time constant	28 ms
Inrush power in W	5.4 W (at 20 °C)
Hold-in power consumption in W	5.4 W at 20 °C
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non-overlap time	1.5 ms on energisation between NC and NO contact     1.5 ms on de-energisation between NC and NO contact
Insulation resistance	> 10 MOhm
Mechanical robustness	Shocks control relay open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks control relay closed: 15 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations control relay open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations control relay closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6
Height	77 mm
Width	45 mm
Depth	93 mm
Net weight	0.58 kg
Environment	
Standards	BS 4794 EN 60947-5 IEC 60947-5-1

LIMIOIIIIEII	
Standards	BS 4794 EN 60947-5 IEC 60947-5-1 NF C 63-140 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x front face conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-4070 °C
Ambient air temperature for storage	-6080 °C
Operating altitude	3000 m without

### Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

#### Contractual warranty

Warranty 18 months