



Product Data Sheet

www.brannan.co.uk

Professional CFM/CMM Thermo-Anemometer

Product Features

- Air velocity, air flow and air temperature measurements
- User selectable units: m/s, Km/h, MPH, Knots, ft/min
- MAX/MIN/Data hold
- Large backlit LCD
- Low battery indicator
- Auto power off
- Supplied in heavy duty carry case
- Available with 3 point Calibration Certificate traceable to National Standards, on request (order part number: 49/700/0)



Product Specifications

- Air Velocity Range:** 0.3 to 45.0 m/s, 1.0 to 162 km/hr
59 to 8858 ft/min, 0.5 to 87.5 knots
0.6 to 100.6 Mph
- Temperature Range:** -30 to 60°C (22 to 140°F)
- Operating Conditions:** -20 to 60°C < 90%RH (non-condensing)
Up to 2000m above sea level
- Storage Conditions:** -30 to 70°C < 75%RH
- Air Velocity Accuracy:** 3% +/- 0.1
- Air Velocity Resolution:** 0.1m/s
- Temperature Accuracy:** +/-1.5°C (+/-2.7°F)
- Sampling Rate:** 1 per second
- Area Set:** 0.001 to 9999m² (0.001 to 9999ft²)
- Battery:** 1 x 9V (included)
- CE & RoHS/WEEE:** Compliant
- Hazard Information (SDS):** See www.brannan.co.uk for information
- LCD Dimensions:** 55 x 45mm
- Product Dimensions:** Packaged: 290 x 355 x 90mm
Unpackaged: 185 x 66 x 33mm
- Product Gross Weight:** Packaged: 1404g
- Component Weights:** Meter: 332g
Case: 868g
Box: 204g



Description	Barcode	Product No
Professional CFM/CMM Thermo-Anemometer	5 011405 134608	13/460/0

PDS 0252:17:R6

Please note: all information on this data sheet is correct at the time of printing, but our policy is one of continuous product development. We reserve the right to change specification without notice.

