

4:1 Dual Wall Heat Shrink Tubing Kit Black

pro-POWER

RoHS
Compliant



Features

- Operating temperature -45°C to +125°C
- Minimum shrink temperature 70°C
- Full recovery temperature 125°C
- Shrink Ratio 4:1
- Approvals: UL224, 125°C 600V VW-1
- Colour: Black

Applications

Manufactured by co-extrusion of polyolefin and hot-melt adhesive. Designed to provide both insulation and sealing for protected articles. Used to protect auto wires, shipping cable, bundle wires and metal tubes against water and moisture. A high expansion ratio makes it possible to repair the most damaged cable jackets without removing connectors.

Kit Contains

- 4mm (45mm length) × 50
- 6mm (45mm length) × 30
- 8mm (70mm length) × 20
- 12mm (70mm length) × 10
- 16mm (70mm Length) × 10

Technical Data - Out Jacket Material

Property	Test Method	Typical Data
Tensile Strength	ASTM D2671	≥12 Mpa
Ultimate Elongation	ASTM D 2671	≥300%
Longitudinal Shrinkage	UL 224	±8%
Heat Aging Ultimate Elongation	158°C, 168hrs	≥200%
Flammability	VW-1	Pass (out jacket only)
Dielectric Strength	IEC 243	≥15kV/mm
Volume Resistivity (ohm-cm)	UL224	≥10 ¹⁴ Ω.cm
Copper Stability	ASTM D 2671	Pass
Corrosion	UL224	No Corrosion

Technical Data - Adhesive

Property	Test Method	Typical Data
Water Absorption	ISO 62	<0.2%
Softening Point	ASTM D E28	95°C
Peel Strength (to PE)	ASTM D 1000	120N/25m
Peel Strength (to AL)	ASTM D 1000	80N/25m

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-POWER

4:1 Dual Wall Heat Shrink Tubing Kit Black



Product Dimensions

Size		As supplied	After Recovery		
Inch	mm	Internal diameter Min.(mm)	Internal diameter Max.(mm)	Total Wall Thickness(mm)	Wall Thickness of Adhesive
5/32	4	4	1	1.05 ±0.3	0.5 ±0.3
1/4	6	6	1.5	1.15 ±0.3	0.5 ±0.3
5/16	8	8	2	1.55 ±0.3	0.6 ±0.3
1/2	12	12	3	1.75 ±0.3	0.6 ±0.3
5/8	16	16	4	2 ±0.3	0.7 ±0.3

Part Number Table

Description	Part Number
Heat Shrink Tubing Kit, Polyolefin, 4:1, Dual Wall, Black, 120 Pcs	HSKIT4:1DUALWALL

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

