



Main

Range	TeSys
Device short name	VZ
Product or component type	Additional earthing block
Performance level	High performance
Contacts type and composition	Without
Product compatibility	V0 V02 V2 V01 V1
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Mounting location	Right Left
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	40 A
Connections - terminals	Screw clamp terminals
Height	74 mm
Width	16 mm
Depth	35 mm
Net weight	0.05 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60947-3
Product certifications	UL GL CSA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (5 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Offer Sustainability

Sustainable offer status	Green Premium product
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------