


Data Sheet

Type Number: 6220
Designation IEC: CR 1220
System: Li-Manganese dioxide / Organic Electrolyte
UL Recognition: MH 13654 (N)
Nominal Voltage [V]: 3
Typical Capacity C [mAh]: 35
 Load 39 kOhm, at 20 °C down to 2.0 V
Weight, approx [g]: 0,8
Volume [ccm]: 0,2
Coding: Manufacturing Month/Year by Letter Code



Temperature Ranges [° C]:

	min.	max.
Storage:	-55	70
Discharge:	-20	65

Dimensions [mm]:

	min.	max.
Diameter [A]:	12,2	12,5
Height [B]:	1,8	2
Shoulder Diameter[E]:	10	
Shoulder Height [C]:	0,3	

Segment: Electronic

Main Applications: Watch
 Photo
 Electronic

Typical Capacities (at 20° C):

Discharge Type:	Load	End Voltage:	2.0 V
Continuous	39000	Ω Time:	480 h
24h/d,7d/w		Capacity [mAh]:	35
Current [µA]:		Energy [mWh]:	100