

2-Port HDMI Splitter - HDMI 2.0, 4K @ 60 Hz, 4:4:4, Multi-Resolution Support, HDR, HDCP 2.2, TAA

MODEL NUMBER: **B118-002-HDR**



Splitter with multi-resolution support transmits 4K x 2K video and audio from an HDMI source to two HDMI displays at the same time.

Features

HDMI Splitter Transmits 4K Video + Audio to 2 HDMI Displays at the Same Time

Recommended for home theaters or short-distance digital signage applications in classrooms, offices, churches, restaurants, bars, hotels and trade shows, this Ultra High Definition (UHD) HDMI splitter is quick and easy to install. It connects to an HDMI source device, such as a computer or Blu-ray player, and transmits a 4K audio/video signal to two HDMI monitors, projectors or televisions simultaneously. You can cascade up to three levels of splitters, which expands the total number of connected displays to eight. Note: You can expand the total up to 64 by including multiple B118-004-HDR splitters (sold separately) in the three-level cascade.

Supports UHD 4K x 2K Signals up to 15 ft. via HDMI Cabling

Using standard 28 AWG HDMI cable, the B118-002-HDR distributes a 4K x 2K audio/video signal (at 60 Hz) up to 15 feet (4 meters). Be sure the HDMI cables connecting the splitter to the source and displays are no longer than 15 feet. For best performance, we recommend using Tripp Lite's P569-Series Premium High-Speed HDMI cables.

Multi-Resolution Support Allows Mixing and Matching of Displays of Different Resolutions

Say you have a brand new 4K (at 60 Hz) HDTV in the living room, but want to also connect your Blu-ray player or satellite box to the older 1080p TV in the bedroom. The B118-002-HDR is backward compatible with 4K x 2K (at 30 Hz) and 1080p (at 60 Hz) resolutions via automatic DIP switching. This splitter allows each television to display video at its maximum resolution. Most other splitters default each television to the lowest common resolution (meaning you would only get a 1080p image on that new 4K TV).

Supports Up-To-Date Features and Formats

The B118-002-HDR supports a wide range of audio formats, including DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1-channel surround sound. It also features lip sync pass-through, xvYCC and x.vColor, and video amplifier bandwidth of 600 MHz/6 Gbps per channel (18 Gbps total). To ensure compatibility with the latest hardware, this splitter is compliant with HDCP 2.2 and HDMI 2.0 standards for carrying HDR (high dynamic range) signals. It supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor, as well as 36-bit Deep Color (12 bits per channel).

Ready to Use Right Out of the Package

Highlights

- Transmits up to 15 ft. for digital signage in bars, offices, classrooms, trade shows, etc.
- Supports UHD resolutions up to 4096 x 2160 (@ 60 Hz) for crystal-clear 4K x 2K video
- Supports multi-resolution output to allow for combination of different display types
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Capable of cascading up to 64 total displays in sophisticated applications
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Watch 4K video content from a notebook, Blu-ray player, cable/satellite box, video game console or media server on multiple televisions or projectors
- Connect a MacBook Pro to give a video presentation on multiple 4K screens
- Attach multiple 4K monitors to your PC to allow easier multitasking or more convenient video editing
- Play online or PC video games that display optimal graphics
- Send Ultra HD content to digital signs or point-of-sale displays
- Connect a security camera or other A/V surveillance



The plug-and-play B118-002-HDR requires no additional software or drivers. Connect your devices to the HDMI ports with user-supplied HDMI cables (such as Tripp Lite's P569-Series), and plug the included external power supply (with four international plug adapters to ensure use all over the world) into an AC power source to get started. A green LED indicates the unit is receiving power, and orange LEDs indicate connected HDMI inputs. Use the included hardware to install the unit on a desktop or mount it to a wall.

TAA-Compliant for GSA Schedule Purchases

The B118-002-HDR is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

equipment to multiple displays

System Requirements

- Source device with HDMI output
- Display device(s) with HDMI input

Package Includes

- B118-002-HDR 2-Port HDMI 2.0 Splitter with Multi-Resolution Support
- External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- International plug adapters (North America, Europe, U.K. and Australia)
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332237972
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60HZ, 0.35A
External Power Supply Output Specs (V / A)	5V, 2A
External Power Supply Cord Length (ft.)	4.0
External Power Supply Cord Length (m.)	1.2
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 5-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; PSE; C-Tick; GS; RoHS
Bus Powered	No



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x1) Green (Power), (x2) Orange (Signal)
PHYSICAL	
Color	Black
Material of Construction	Metal
Rackmountable	Yes
Unit Dimensions (hwd / cm)	2.69 x 11.51 x 6.24
Unit Dimensions (hwd / in.)	1.06 X 4.53 X 2.46
Unit Packaging Type	Box
Unit Weight (kg)	0.22
Unit Weight (lbs.)	0.49
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	0% to 85% RH, Non-Condensing
CONNECTIONS	
Ports	2
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
Connector Plating	Nickel
PORT EXPANSION	
Max Distance (Between any 2 Units)	10ft
Max Number of Ports (Entire Chain)	32
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	4096 x 2160 60Hz
HDMI Specification	2.0
HDCP Specification	2.2
Audio Specification	DTS-HD, Dolby TrueHD, Dolby Digital Plus, and LPCM 7.1 Channel Surround Sound
Driver Required	No
Max Supported Color Depth	36-bit Deep Color
EDID Compatible	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

3D Video Supported	Yes
Technology	HDMI
SPECIAL FEATURES	
HDR Support	Yes
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>