


## Label - US-EMLF (15X6) YE - 0803832

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 15 x 6 mm, Number of individual labels: 132



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 055626 172644
GTIN	4055626172644
Weight per Piece (excluding packing)	6.010 g
Custom tariff number	39199080
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	6 mm
Width (a)	15 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

#### General

Color	yellow
Components	Silicone-free
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

# Label - US-EMLF (15X6) YE - 0803832

## Technical data

### General

Number of individual labels	132
Number of individual labels per row	6
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Procedure	A
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Marking mounting type	adhesive

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Environmental Product Compliance

REACH SVHC	Reaction mass of DOTE and MOTE
------------	--------------------------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

### ETIM

ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

### UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504

## Label - US-EMLF (15X6) YE - 0803832

### Classifications

#### UNSPSC

UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

#### Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards