

Antenna cable - RAD-CAB-PFP240-10 - 5606124

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna cable, outside diameter: 6 mm (0.24 in.), inner conductor: solid, attenuation: 1.0 / 1.5 / 2.1 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2x N (male), cable length: 3 m (10 ft.)




Your advantages

- For outdoor installation
- UV resistant



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 685399
GTIN	4046356685399
Weight per Piece (excluding packing)	206.300 g
Custom tariff number	85442000
Country of origin	China
Note	Made to Order (non-returnable)

Technical data

Dimensions

Fixed cable length	3 m
--------------------	-----

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Connection 1	Connector connection
Connection method	Type N (male)
Note	Both sides
Cable type	PFP-240

Antenna cable - RAD-CAB-PFP240-10 - 5606124

Technical data

General

External sheath, color	black
Frequency range	400 MHz ... 5.8 GHz
Impedance	50 Ω

Attenuation

868 / 900 MHz	1 dB
2.4 GHz	1.5 dB
5 GHz	2.1 dB

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	19070102
eCl@ss 5.1	19070100
eCl@ss 6.0	19070100
eCl@ss 7.0	19070102
eCl@ss 8.0	27060310
eCl@ss 9.0	27060310

ETIM

ETIM 3.0	EC001698
ETIM 4.0	EC000019
ETIM 5.0	EC001682
ETIM 6.0	EC001682
ETIM 7.0	EC001682

UNSPSC

UNSPSC 6.01	43171611
UNSPSC 7.0901	43221706
UNSPSC 11	43171611
UNSPSC 12.01	43221706
UNSPSC 13.2	26121606
UNSPSC 18.0	26121606
UNSPSC 19.0	26121606
UNSPSC 20.0	26121606
UNSPSC 21.0	26121606

