



DATASHEET Part No. 1004627 Product: **GPS/GLONASS** Patch Antenna with Cable

# Part No. 1004627 **GPS/GLONASS** Patch Antenna with Cable

1.575, 1.602 GHz

Supports: Tracking, Smart Home, Agriculture, Automotive, Healthcare, Digital Signage, Wearables, Industrial Devices



By optimizing antenna size,

performance and emissions, customer and regulatory

•

OBD-II

Access

Point **Telematics**  Ethertronics' antennas deliver on the key needs of device designers for higher functionality and performance in smaller/thinner designs. These innovative antennas provide compelling advantages for a GPS/GLONASS enabled handheld devices, media players and other mobile devices.

### **Electrical Specifications**

Typical characteristics measured on a 70 x 70 mm PCB ground plane.

and the second sec	Frequency (GHz)	1.575	1.602		
GPS / GLONASS Patch Antenna 1.575 & 1.602 GHz	GNSS Bands	GPS	GLONASS		
	Peak Gain	3.7 dBi	3.0 dBi		
	Gain at Zenith	3.59 dBic	1.04 dBic		
KEY BENEFITS Reduced Costs & Time-to-Market Standard antennas eliminate design fees, redesign cycle time and minimize risk associated with	Axial Ratio	1.0 dB	8.0 dB		
	Average Efficiency	60%	36%		
	VSWR	< 2.0:1	< 3.0:1		
	Polarization	R.H.C.P			
customer solution. Quicker time to market.	Feed Point Impedance	50 Ω			
Quicker Time-to-Market					

## Mechanical Specifications & Ordering Part Number

periornance and c	cimoolono,		
customer and regulatory specifications are more easily met. Reliability Products are the latest RoHS version compliant. APPLICATIONS		Ordering Part Number	1004627
		Size (mm)	25.0 x 25.0 x 5.3
		Mounting	Drop-in (Adhesive)
		Weight (grams)	6.8
	racking lealthcare	Packaging	Plastic Tray
POS, POS, M2M, Headsets, Industrial		Connector	IPEX MHF3
	levices Smart Grid	Cable (mm)	Gray Ø 0.81 coax , 72.0 cable

## 10/1/2019


Proprietary





GPS / GLONASS Patch Ethertronics' Embedded Antenna Specifications Ethertronics produces a wide variety of standard and custom antennas to meet user needs.


VSWR, Efficiency, Peak Gain, and Axial Ratio Plots Typical performance on 70 x 70 mm PCB

> Teste Setup: 1004627 GPS antenna (25 x 25 x 5.3 mm, 72mm cable) On 70 x 70 mm ground plane










#### Axial Ratio (1585 MHz)



tel +(1) 858.550.3820 | fax +(1) 858.550.3821 email: eth.info@avx.com 5501 Oberlin Drive, Suite 100 San Diego, CA 92121 - USA




GPS / GLONASS Patch Ethertronics' Embedded Antenna Specifications Ethertronics produces a wide variety of standard and custom antennas to meet user needs.

#### **Antenna Radiation Patterns**


Typical performance on 70 x 70 mm PCB Measured @ 1575, 1600 MHz





90




►Z










90



tel +(1) 858.550.3820 | fax +(1) 858.550.3821 email: eth.info@avx.com 5501 Oberlin Drive, Suite 100 San Diego, CA 92121 - USA



GPS / GLONASS Patch Ethertronics' Embedded Antenna Specifications Ethertronics produces a wide variety of standard and custom antennas to meet user needs.

#### **Mechanical Dimensions**

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm)
1004627	25.0 ± 0.2	25.0 ± 0.2	5.3	72.0 ± 2.0

