An economical solid-state TDR with octal plug-in base, the 339 maintains excellent repeat accuracy despite wide voltage and temperature variations/ even after long periods of down-time. Two models are available. Each has six dial selected ranges from fractions of a second to as long as 10 hours. Each model has a selectable on-delay or interval timing mode.

WIDE CHOICE OF RANGES: In addition to the short ranges expected of an electronic TDR, the 339 is also available with ranges as long as 10 hours. An unusually versatile timer, the 339 has six dial-selected ranges—from 0.3 seconds to 3 hours or 1 second to 10 hours—and provides dial-adjustable timing periods between 0.075 seconds and 10 hours. A single 339 model thus accommodates the needs of a wide range of applications, allowing the user to select easily and precisely—an appropriate range to permit optimum setting accuracy. The dial face automatically displays the selected range.

CYCLE PROGRESS INDICATION: The 339's LED annunciator provides a unique and effective method of cycle progress indication. Off before timing, the LED blinks at an ever-increasing rate as the cycle progresses; once every 3-1/2 seconds during the first 10% of the cycle, twice during the second 10%, and so on. At time-out, the LED stays on constantly, pulsing at a high rate. (In the 1 and 10-second ranges, the LED is off before timing, steady on during timing, and pulsing on after time-out.)

HIGH ACCURACY: The 339's timing circuit is not a simple RC circuit, but includes counting technology along with a stable oscillator to provide repeatable time delays.

MULTIPLE TIMING MODES: Every 339 can be used for either on-delay or interval timing operation. The timing mode is selectable by a switch on the 339 housing.

OPERATION

Timing begins when the start switch is closed. This starts an oscillator which runs at a frequency determined by the time setting. A fixed number of counts from the oscillator determines the end of the time cycle. The time required to accomplish this depends on the oscillator frequency. During timing, a LED located on the dial face blinks. For the first ten percent of the cycle, the LED repeatedly blinks once followed by a pause, for the second 10%, it blinks twice and so on indicating the cycle progress. It flashes rapidly and continuously after time out.

ON-DELAY MODE: At time out, the built-in relay transfers its contacts. These contacts remain transferred until the start switch is opened or power is removed by some other means. The 339 then resets and is ready for another cycle.

INTERVAL MODE: When timing begins, the built-in relay transfers its contacts. The contacts remain transferred until time out. The timer will not start again until the start switch is opened or power is removed by some other means. The 339 then resets and is ready for another cycle.









Plug-In Adjustable Time Delay Relay


MODEL NUMBER


MODEL NUMBER	339B				
RANGE					
Six dial-selected ranges 359					
(.3 or 3 SEC, M					
Six dial-selected ranges		200			
(1 or 10 SEC, MIN, HR)					
VOLTAGE & FREQUENCY					
120 VAC, 50/60 Hz			Q		
240 VAC, 50/60 Hz			R		
24 VAC, 50/60 Hz, 24 VDC			T		
12 VDC			E		
ARRANGEMENT					
ON-Delay, Interval Mode				2	
Special				0	
FEATURES					
Standard					Х
Special					K

ACCESSORIES

8-Pin surface/DIN rail socket	000-825-85-00			
Hold down for above socket	339-025-03-00			
(2 required)				
Plug-in socket kit (8-pin)	319-261-45-00			

WIRING









SPECIFICATIONS **MODELS** Choice of two multi-range units. All models operate in on-delay or interval mode. **RANGES** Choice of two models Six dial-selected ranges: 1.0 and 10 SEC, MIN, HR or 0.3 and 3 SEC, MIN, HR 3% of range, except 75 mSEC on 0.3 SEC and **MINIMUM SETTING** 1.0 SEC ranges. **LOAD RELAY TYPE** DPDT 10 AMPS resistive at 30 VDC or 250 VAC (or less) 1/8 HP @120 VAC LIFE 10 million operations with no load 100,000 operations with:10 AMPS at 30 VDC (or less) or 10 AMPS at 250 VAC (or less) CONTACT Silver Cadmium Oxide **MATERIAL** 0° to 140°F (-17° to 60°C) **TEMPERATURE RATING MOUNTING** Plug-in octal base; mounts in any position with retaining clips. OPTIONS: Surface mounting socket DIN rail mounting socket Panel-mounting adapter kit Plug-on socket Rear facing terminal socket. 95 - 132 VAC,50/60Hz **POWER** 120 VAC REQUIREMENTS Inrush - .4A Running - .025 240 VAC 190 - 264 VAC, 50/60 Hz Inrush - .2A Running - .013A 24 VAC/DC 19.2 - 26.4 VAC/DC Inrush - .4A Running - .075A 12 VDC 9.6 - 13.2 VDC Inrush - .25A Running - .10A REPEAT ACCURACY Varies as a function of line voltage and temperature but not of reset time $\pm 0.5\%$ at constant temperature and voltage. (or ± 15 mSEC whichever is greater) ± 1%* at constant voltage and full temperature range. (or \pm 25 mSEC which ever is greater) \pm 1.5%* at constant temperature and full voltage range. (or ± 25 mSEC whichever is greater) \pm 2%* over full voltage and temperature range. (or \pm 30 mSEC, which ever is greater) *Variations of line voltage must be within 95 and 132V; of temperature between -17° and 60°C (0° and 140°F) **RECYCLE** The timer can be used as a pulse generator with L1 power **CHARACTERISTICS** wired though its NC contacts. The pulse will be 35 mSEC to 90 mSEC long. (40 mSEC typical pulse.) 0 to 20 mSEC power interruption; Guaranteed no reset. 20 mSEC to 90 mSEC; it may reset. (40 mSEC typical reset). Over 90 mSEC guaranteed to reset. The TDR will reset

DIMENSIONS (INCHES/MILLIMETERS)






00008258500 SOCKET WITH 339-025-03-00 HOLD DOWNS

2.5 oz. (70 q)


properly and not start timing when subjected to an open start switch leakage of 1.5 mA or less. (Prox switch and Triac drive applications)

WEIGHT

132




8 and 11-Pin Base Mount/Din Rail Sockets



600-3-0018 DIN Rail or Base Mount, 4PDT, Miniature Relay Socket 30mm (W) x 71.5mm (T) x 29mm (D)




600-3-0019
DIN Rail or Base Mount, DPDT for
.187 Terminal Relays (10 Amp.) Socket
32mm (W) x 67mm (T) x 27mm (D)




600-3-0011 Panel Mount, 8 Pin 43.5mm (W) x 43.5mm (T) x 20mm (D)



600-3-0012 Panel Mount, 11 Pin 47mm (W) x 47mm (T) x 20mm (D)



600-3-0013 DIN Rail or Base Mount, 8 Pin 43.5mm (W) x 43.5mm (T) x 20mm (D)




600-3-0014 DIN Rail or Base Mount, 11 Pin 47mm (W) x 47mm (T) x 20mm (D)

1/16 DIN TIMER ACCESSORIES—8 PIN ACCESSORIES

000-825-85-00

8-Pin surface DIN rail socket. Recommended for use with all 8-pin octal plug-in devices when surface mounting or DIN rail mounting.






API 008FS


8-Pin Finger-Safe Socket.






319-261-45-00

Plug-on socket kit (8 pin). Recommended for use with all 8-pin octal plug-in devices. Panel mounting only. Attach the wires to the solderless connector with a crimping tool.






405-320-02-00

Panel Mounting bracket. Recommended for use with all 1/16 DIN timers when panel mounting. Use in conjunction with the 8-pin or 11-pin panel socket with rear facing terminals.






407-025-13-00

Hold-down for part #000-825-85-00. Two (2) needed for proper installation.






1/16 DIN TIMER ACCESSORIES—8 PIN ACCESSORIES

000-825-86-00


11-Pin surface DIN rail socket. Recommended for use with all 11-pin octal plug-in devices when surface mounting or DIN rail mounting.






70-463-1

11-Pin Socket, DIN/Panel Mount, with screw terminals & Clamping plates.






314-260-07-00

Plug-on socket kit (11-pin).
Recommended for use with all 11-pin octal plug-in devices. Panel mounting only. Attach the wires to the solderless connector with a crimping tool.






405-025-07-00

Hold down for part #000-825-86-00. Two (2) needed for proper installation.






101-026-105

Recommended for use with all the ATC Diversified Electronics family of "remote adjustable" timers. Proper spacing is maintained for UL and CSA applications. This linear taper potentiometer has a non-conductive shaft attached to the internal conductive plastic wafer. The brass bushing is 3/8" x 32NEF and accepts adjustment hardware 1000540070, 100054071.





100-054-073

Recommended for use with any adjustment or switch having a 1/4" shaft. This knob slips over the shaft and is secured in place by a #6-32 set screw. The knurled, mirror finished, black thermostat knob has a white pointer line for reference.



