

TL70 Multicolor RGB Tower Light Module



Datasheet



For more information regarding TL70 Multicolor RGB Tower Light final assemblies, including wiring diagrams, refer to the following documents:

- TL70 Modular Tower Light datasheet (p/n 182214)
- TL70 Wireless Modular Tower Light datasheet (p/n 185469)
- TL70 Modular Tower Light AC voltage datasheet (p/n 191349)

Configuring the Module

Turn on the appropriate DIP switch to set the order of the components, counting up from the tower light's base. Factory default DIP position is OFF.

Assembly Options		Black DIP Switch							
		1B	2B	3B	4B	5B	6B	7B	8B
Color Selection	Red								ON
	Green							ON	
	Yellow							ON	ON
	Blue						ON		
	Magenta						ON		ON
	Cyan						ON	ON	
	White						ON	ON	ON
	Amber					ON			
	Rose					ON			ON
	Lime Green					ON		ON	
	Orange					ON		ON	ON
	Sky Blue					ON	ON		
	Violet					ON	ON		ON
	Spring Green					ON	ON	ON	
	Color Demo								
Flash Demo					ON	ON	ON	ON	

Flashing and Strobing	Solid On							
	0.5 Hz Flash				ON			
	1.5 Hz Flash			ON				
	3.0 Hz Flash			ON	ON			
	0.5 Hz Strobe		ON					
	1.5 Hz Strobe		ON		ON			
	3.0 Hz Strobe		ON	ON				
	Intensity Sweep		ON	ON	ON			
Intensity	High							
	Low	ON						



Assembly Options		White DIP Switches					
		1	2	3	4	5	6
Position	Module 1	ON					
	Module 2		ON				
	Module 3			ON			
	Module 4				ON		
	Module 5					ON	
	Module 6						ON

Specifications

Supply Voltage and Current

12 V dc to 30 V dc
 Maximum current in high intensity mode: 350 mA max. at 12 V dc; 170 mA typical at 24 V dc
 Maximum current in low intensity mode: 140 mA max. at 12 V dc; 70 mA typical at 24 V dc

Supply Protection Circuitry

Protected against transient voltages

Indicator Response Time

Off Response: 150 µs (maximum) at 12 V dc to 30 V dc
 On Response: 40 ms (maximum) at 12 V dc; 50 ms (maximum) at 30 V dc

Indicator Characteristics

Color	Dominant Wavelength (nm) or Color Temperature (CCT)	Color Coordinates ¹		Lumen Output (Typical at 25 °C)
		x	y	
Red	622	0.694	0.304	27.4
Green	527	0.177	0.707	69
Yellow	575	0.456	0.489	46.6
Blue	472	0.128	0.080	17.4
Magenta	-	0.371	0.176	24
Cyan	493	0.161	0.347	49.5
White	5600 K	0.310	0.335	40.9
Amber	589	0.542	0.422	39.9
Rose	-	0.497	0.226	26.6
Lime Green	561	0.369	0.556	53.8
Orange	600	0.606	0.372	35.5
Sky Blue	486	0.146	0.251	41.7
Violet	-	0.222	0.117	21.3
Spring Green	508	0.166	0.531	62.4

Required Overcurrent Protection



WARNING: Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the supplied table.
 Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply.
 Supply wiring leads < 24 AWG shall not be spliced.
 For additional product support, go to www.bannerengineering.com.

Supply Wiring (AWG)	Required Overcurrent Protection (Amps)
20	5.0
22	3.0
24	2.0
26	1.0
28	0.8
30	0.5

Construction

Bases, segments, covers: polycarbonate

Leakage Current Immunity

550 µA

Operating Conditions

-40 °C to +50 °C (-40 °F to +122 °F)
 95% at +50 °C maximum relative humidity (non-condensing)

Environmental Rating

IEC IP65

Vibration and Mechanical Shock

Vibration 10 Hz to 55 Hz 0.5 mm p-p amplitude per IEC 60068-2-6
 Shock 15G 11 ms duration, half sine wave per IEC 60068-2-27

Certifications



Banner Engineering Corp. Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. **IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.**

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change; Banner reserves the right to modify product specifications or update documentation at any time. Specifications and product information in English supersede that which is provided in any other language. For the most recent version of any documentation, refer to: www.bannerengineering.com.

¹ Refer to CIE 1931 chromaticity diagram or color chart, to show equivalent color with indicated color coordinates.