

# RP73PF1J18R2BTDF ✓ ACTIVE

TE Internal #: 4-1625867-6

Surface Mount Resistors, Precision Resistor, 2 Terminations, Size Code 0603, Taped & Reeled, .1%, Thin Film, Resistance Range Up to 1k $\Omega$

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Size Code: **0603**

Packaging Method: **Taped & Reeled**

Tolerance: **.1%**

## Features

### Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Size Code	0603
Element Type	Thin Film

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Voltage Rating	100 V
Tolerance	.1%
Resistance Range	Up to 1k $\Omega$
Resistance	18.2 $\Omega$
Power Rating	.166 W

### Termination Features

Number of Terminations	2
Termination Type	Solder

### Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

### Dimensions

Dimensions	1.55 x .8 x .45 mm
------------	--------------------

### Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts




TE Model / Part # 1-2176092-8  
RP 2A 0.25W 1K0 0.1% 25PPM 1K RL




TE Model / Part # 2176093-5  
RP 2A 0.25W 10K 0.1% 25PPM 1K RL



TE Model / Part # 1625867-2  
RP 1J 0.166W 10K 0.1% 25PPM 1K RL



TE Model / Part # 2176308-5  
RP 1E 0.1W 147K 0.1% 25PPM 5K RL



TE Model / Part # 2-2176308-7  
RP 1E 0.1W 249K 0.1% 25PPM 5K RL

## Customers Also Bought



TE Model / Part #1393258-8  
V23047-A1018-A501



TE Model / Part #5-146253-1  
02 MODII HDR DRST B/A .100CL LF



TE Model / Part #6-104071-7  
40 SYSTEM 50 HDR SRST SHRD SN



TE Model / Part #2-1625867-3  
RP 1J 0.166W 10R5 0.1% 25PPM 1K RL



TE Model / Part #4-1625867-3  
RP 1J 0.166W 16R9 0.1% 25PPM 1K RL



TE Model / Part #7-1625867-7  
RP 1J 0.166W 39R2 0.1% 25PPM 1K RL



TE Model / Part #104693-1  
10 50/50 HDR DRST SFMNT .390



TE Model / Part #2102318-1  
Fortis Zd 10 Col R/A Full Shroud Assy SE



TE Model / Part #YD369-G99-  
NP400000  
369 9 WAY INLINE 90 PCB REC,  
GOLD, PIN



TE Model / Part #YDTS20G19-  
35PNV001  
RECP ASSY



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_4-1625867-6\\_BA.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_4-1625867-6\\_BA.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_4-1625867-6\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[RP73-0915](#)

English