Product data sheet Characteristics

9007C54B2P6 LIMIT SWITCH 600V 10AMP C +OPTIONS



I۱	/[а	Ш	n

Range of product	9007		
Series name	Heavy duty		
Product or component type	Limit switch		
Product specific application	Standard box		
Device short name	9007C	-	
Body type	Plug-in		
Head type	Rotary head		
Material	Metal		
Fixing mode	By the body		
Movement of operating head	Rotary		
Type of operator	Zinc spring return without operating lever (-)9007C lever		
Switch actuation	From left and right CW and CCW		
Type of approach	Lateral approach, 1 or 2 programmable direction		
Electrical connection	Screw-clamp terminals (AWG 22AWG 12), 12		
Cable entry	1 entry for 1/2" - 14 NPT conforming to BS 4568		
Number of poles	1		
Contacts type and composition	NC-NO		
Contact operation	Snap action		
Positive opening	Without		
Sale per indivisible quantity	1		

Complementary

Body material	Zinc	
Head material	Zinc	i i
Function available	-	<u>8</u>
Switch function	SPDT-DB	ation of the control
Contact form	Form Z	E E
Contacts material	Silver contacts	
Terminals description ISO n°1	(3-4)NO (1-2)NC	ner: This
Minimum torque for tripping	4 lbf.in	ic SC

Maximum actuation speed	90 ft/min with 45° cam angle, levers only 130 ft/min with 30° cam angle, levers only		
Tripping angle	10 °		
Maximum displacement angle	90 °		
Repeat accuracy	+/- 0.002 in linear travel of cam		
[le] rated operational current	6 A at 120 V AC, A150 conforming to NEMA 0.55 A at 120 V DC		
[Ithe] conventional enclosed thermal current	10 A		
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to UL 508 for contact block 600 V (pollution degree 3) conforming to CSA C22.2 No 14 for contact block		
[Uimp] rated impulse withstand voltage	2.5 kV AC 1 min conforming to CE 2.2 kV AC 1 min conforming to UL 2.64 kV AC 1 s conforming to CSA		
Short-circuit protection	10 A by CC fuse, protection type: non-time delay		
Electrical durability	1000000 cycles		
Local signalling	1 LED indicator light (light OFF when switch is actuated) at 24120 V AC/DC service life: 100000 h		
Mechanical durability	10000000 cycles		
Width	1.55 in		
Height	4.02 in		
Depth	2.5 in		
Net weight	1.25 lb(US)		

Environment

Shock resistance	60 gn for 9 ms conforming to IEC 60068-2-27			
Vibration resistance	25 gn (f= 10150 Hz) conforming to IEC 60068-2-6			
NEMA degree of protection	NEMA 1 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250			
IP degree of protection	IP67 conforming to IEC 60529			
Electrical shock protection class	Class 0 conforming to IEC 61140			
Ambient air temperature for operation	-20185 °F for standard environment			
Ambient air temperature for storage	-20185 °F			
Environmental characteristic	Standard environment			
Protective treatment	Epoxy powder coat			

Offer Sustainability

REACh Regulation	REACh Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

	<u> </u>			
Warranty		18 months		