



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Differential thermal overload relay
Device short name	LRD
Relay application	Motor protection
Product compatibility	LC1D80A
Network type	AC DC
Thermal overload class	Class 10A
Thermal protection adjustment range	62...80 A
[Ui] rated insulation voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V conforming to UL 60947-4-1 Power circuit: 600 V conforming to CSA C22.2 No 14

Complementary

Network frequency	0...400 Hz
Mounting support	Plate, with terminal block LAD96560 on top Rail, with terminal block LAD96560 on top Direct mounting under contactor
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
Auxiliary contact composition	1 NO + 1 NC
[I _{th}] conventional free air thermal current	5 A for signalling circuit
Permissible current	0.95 A at 380 V AC-15 for signalling circuit 0.06 A at 440 V DC-13 for signalling circuit
[U _e] rated operational voltage	690 V
[U _{imp}] rated impulse withstand voltage	6 kV
Power dissipation per pole	4.8 W
Phase failure sensitivity	Tripping current 130 % of I _r on two phase, the last one at 0

Control type	Red push-button: stop Blue push-button: reset
Temperature compensation	-20...60 °C
Connections - terminals	Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm ² flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm ² solid Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² solid Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm ² flexible Power circuit: direct terminal link on top
Tightening torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 25 mm ² Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 35 mm ²
Height	70 mm
Width	55 mm
Depth	123 mm
Net weight	0.375 kg
Colour	Grey (SE GREY 6)

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-60...70 °C
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 Gn conforming to IEC 60068-2-6
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	EN/IEC 60947-4-1 ATEX D 94/9/CE EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 14
Product certifications	EAC ATEX INERIS CCC

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information