

# testo Smart Probes - mould kit

### testo 605i thermohygrometer testo 805i infrared thermometer in the testo Smart Case

Identify mould risk early with the testo Smart Probes App

Measurement spot marking with laser function

Presentation and evaluation of the mould risk in traffic-light colours

Measurement data analysis and dispatch incl. photo documentation of the affected areas via testo Smart Probes App



The testo Smart Probes mould kit, in combination with the free testo Smart Probes App, is ideal for preventive mould risk identification before this can even occur. This compact and easy-to-transport kit contains two testo Smart Probes testo 605i and testo 805i for measuring ambient temperature, relative air humidity and surface temperature. This makes it perfect for fast identification of mould danger. The results of the the mould indication are evaluated according to the traffic light principle (green, yellow, red), and can be saved at the press of a button as a PDF, CSV or Excel file, and transferred to other devices or sent directly by email. For the purposes of better visualisation, photos of the affected area are added to the report.



## Technical data/accessories

## testo Smart Probes mould kit

testo Smart Probes – mould kit for the preventive identification of mould. Consists of: testo 605i, testo 805i, testo Smart Case (IAQ), batteries, calibration protocol



Order no. 0563 0005 10



#### testo Smart Probes App

The App turns your smartphone/tablet into the display for up to 6 Testo Smart Probes at the same time. Both the operation of the measuring instruments and the display of the readings are achieved by Bluetooth® via the testo Smart Probes App on your smartphone or tablet – independently of the measuring location. In addition, you can use the App to create measurement reports, add photos and comments to these and send them by e-mail. For iOS and Android.

	testo 605i	testo 805i
Sensor type	Humidity - capacitive	Infrared
Measuring range	0 to 100 %RH	-30 to +250 °C
Accuracy	±3.0 %RH (10 to 35 %RH)	±1.5 °C or ±1.5% of m.v. (0 to +250 °C)
±1 digit	±2.0 %RH (35 to 65 %RH)	$\pm 2.0$ °C (-20 to -0.1 °C)
	+5 %BH (< 10 %BH or > 90 %BH)	±2.3 C (-30 to -20.1 C)
	(at +25 °C)	
Resolution	0.1 %RH	≤0.1 °C
Sensor type	NTC	
Measuring range	-20 to +60 °C	
Accuracy	±0.8 °C (-20 to 0 °C)	
±1 digit	±0.5 °C (0 to +60 °C)	
Resolution	≤0.1 °C	
Compatibility	requires iOS 8.3 or newer / Android 4.3 or newer	
	requires mobile end dev	vice with Bluetooth <sup>®</sup> 4.0
Bluetooth <sup>®</sup> range	up to 100 m	up to 15 m
Storage temperature	-20 to +60 °C	-20 to +60 °C
Operating temperature	-20 to +50 °C	-10 to +50 °C
Battery type	3 micro batteries AAA	3 micro batteries AAA
Battery life	150 hrs	30 hrs
Dimensions	218 x 30 x 25 mm	140 x 36 x 25 mm
	73 mm probe shaft	
Optics		10:1
Laser marking		diffractive optics (laser circle)
Emissivity		0.1 to 1.0 adjustable



1981 1924/msp/I/04.2019