## Product data sheet Characteristics

## LC1D65M7S335

TeSys D contactor S335 - 3P (3NO) AC-3 <= 440V 65A - 220V AC coil



Range	TeSys	
Product name	TeSys D	
Product or component type	Contactor	
Device short name	LC1D	
Contactor application	Motor control Resistive load	
Utilisation category	AC-3 AC-1	
Poles description	3P	
Power pole contact composition	3 NO	
[Ue] rated operational voltage	Power circuit: <= 1000 V AC 25400 Hz	
[le] rated operational current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3 for power circuit	
Motor power kW	18.5 kW at 220/230 V AC 50 Hz (AC-3) 30 kW at 380/400 V AC 50 Hz (AC-3) 37 kW at 415 V AC 50 Hz (AC-3) 37 kW at 440 V AC 50 Hz (AC-3) 37 kW at 500 V AC 50 Hz (AC-3) 37 kW at 660/690 V AC 50 Hz (AC-3) 37 kW at 1000 V AC 50 Hz (AC-3)	
Motor power HP (UL / CSA)	40 hp at 460/480 V AC 60 Hz for 3 phases motors 5 hp at 115 V AC 60 Hz for 1 phase motors 10 hp at 230/240 V AC 60 Hz for 1 phase motors 20 hp at 200/208 V AC 60 Hz for 3 phases motors 20 hp at 230/240 V AC 60 Hz for 3 phases motors 50 hp at 575/600 V AC 60 Hz for 3 phases motors	
[Uc] control circuit voltage	220 V AC 50/60 Hz	
Auxiliary contact composition	1 NO + 1 NC	
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947	
Overvoltage category	III	
[lth] conventional free air thermal current	80 A (at 60 °C) for power circuit 10 A (at 60 °C) for control circuit	
Irms rated making capacity	250 A DC for signalling circuit conforming to IEC 60947-5-1 1000 A at 440 V AC for power circuit conforming to IEC 60947 140 A AC for control circuit conforming to IEC 60947-5-1	
Rated breaking capacity	1000 A at 440 V for power circuit conforming to IEC 60947	
[lcw] rated short-time withstand current	110 A 40 °C - 10 min for power circuit	

	260 A 40 °C - 1 min for power circuit 520 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated fuse rating	125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1
Average impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
[Ui] rated insulation voltage	Power circuit: 1000 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
Electrical durability	1.4 Mcycles 80 A AC-1 at Ue <= 440 V 1.45 Mcycles 65 A AC-3 at Ue <= 440 V
Power dissipation per pole	9.6 W AC-1 6.3 W AC-3
Safety cover	With
Mounting support	Rail Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 EN 60335-1
Product certifications	IEC UL CSA CCC
Connections - terminals	Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid Power circuit: screw connectors 1 cable(s) 2.525 mm²solid Power circuit: screw connectors 2 cable(s) 2.516 mm²solid Power circuit: screw connectors 1 cable(s) 2.525 mm²flexible with cable end Power circuit: screw connectors 2 cable(s) 2.510 mm²flexible with cable end Power circuit: screw connectors 1 cable(s) 2.525 mm²flexible without cable end Power circuit: screw connectors 2 cable(s) 2.516 mm²flexible without cable end
Tightening torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 to Ø 8 mm
Mechanical durability	6 Mcycles
Maximum operating rate	3600 cyc/h 60 °C
Complementary	
Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.851.1 Uc 55 °C operational AC 60 Hz 0.30.6 Uc 55 °C drop-out AC 50/60 Hz 0.81.1 Uc 55 °C operational AC 50 Hz
Inrush nower in VA	245 VA 50/60 Hz cos phi 0.75 (at 20 °C)

Coil technology	Without built-in suppressor module	
Control circuit voltage limits	0.851.1 Uc 55 °C operational AC 60 Hz 0.30.6 Uc 55 °C drop-out AC 50/60 Hz 0.81.1 Uc 55 °C operational AC 50 Hz	
Inrush power in VA	245 VA 50/60 Hz cos phi 0.75 (at 20 °C)	
Hold-in power consumption in VA	26 VA (at 20 °C) cos phi 0.3 50/60 Hz	
Heat dissipation	610 W at 50/60 Hz	
Auxiliary contacts type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling circuit frequency	25400 Hz	
Minimum switching current	5 mA for signalling circuit	
Minimum switching voltage	17 V for signalling circuit	
Non-overlap time	1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact	
Insulation resistance	> 10 MOhm for signalling circuit	

## Environment

IP degree of protection	IP20 front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	-560 °C
Ambient air temperature for storage	-6080 °C
Permissible ambient air temperature around the device	-4070 °C at Uc
Operating altitude	3000 m without
Fire resistance	850 °C conforming to IEC 60695-2-1
Flame retardance	V0 conforming to UL 94
Mechanical robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor open: 8 Gn for 11 ms Shocks contactor closed: 10 Gn for 11 ms
Height	127 mm
Width	75 mm
Depth	119 mm
Net weight	1.4 kg