


Proximity sensor SME-8M-DO-24V-K-7,5-OE

Part number: 546799

FESTO



Data sheet

Feature	Value
Type code	SME
Symbol	00991622
Certification	c UL us - Listed (OL) RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
Special features	Oil-resistant
Note on materials	Free of copper and PTFE RoHS-compliant
Measuring principle	Magnetic reed
Ambient temperature	-40 °C ... 70 °C
Switching output	Contact-based, bipolar
Switching element function	N/C contact
Max. output current	80 mA
Max. output current in mounting kits	80 mA
Min. switching capacity AC	2.4 VA
Max. switching capacity DC	2.4 W
Max. switching capacity DC in mounting kits	2.4 W
Max. switching capacity AC in mounting kits	2.4 VA
Voltage drop	4.25 V
Short-circuit protection	no
Overload protection	Not available
Operating voltage range AC	5 V ... 30 V
DC operating voltage range	5 V ... 30 V
Reverse polarity protection	no
Electrical connection	Cable 3-wire
Connection outlet orientation	Longitudinal
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Cable chain: 5 million cycles, bending radius 75 mm
Cable length	7.5 m
Cable characteristic	Standard + cable chain
Material of cable sheath	TPE-U(PUR)
Type of mounting	Can be inserted in slot from above Screwed tightly
Product weight	87.1 g
Housing material	PA High-alloy stainless steel

Feature	Value
Switching status indication	LED yellow
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Degree of protection	IP68 IP65