

M35/16



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	M35/16
Product ID:	1SNA115124R0700
EAN:	3472591151244
Catalog Description:	M35/16 Screw Clamp Terminal Blocks - Feed-through - Grey
Long Description:	- Closed terminal block: no end section needed, optimized rigidity, - Flexibility: snap onto symmetrical and asymmetrical rails, - Use of Jumper bars requires the user to cut out the partition.

Ordering

Color:	Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	16 mm
Product Net Height:	49 mm
Product Net Depth / Length:	46.5 mm
Product Net Weight:	30 g

Technical

Rated Cross-Section:	35 mm ²
Spacing:	16 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 6 ... 35 mm ² Screw Clamp / Rigid 1x 6 ... 50 mm ² Screw Clamp / With Insulated Ferrule 1x 35 mm ²
Gauge Type:	B9
Rated Current (I_n):	Main Circuit 125 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 4200 A

Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	3500 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	17.0 mm
Recommended Screw Driver:	6.5 ... 7 mm
Tightening Torque:	acc. IEC 60947-1 2.8 N·m Manufacturer 3 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 10 ... 0 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 10 ... 0 AWG Stranded 0 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

CB Certificate:	1SND161028A0203
CSA Certificate:	1SND161052A0202
cUL Certificate:	1SND161001A0209
Declaration of Conformity - CE:	1SND225014U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220001E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
E-nummer:	2925516
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	81 mm
Package Level 1 Depth / Length:	200 mm
Package Level 1 Height:	53 mm
Package Level 1 Gross Weight:	0.62 kg
Package Level 1 EAN:	3472591151244
Package Level 2 Units:	300 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 2 Gross Weight:	15.350 kg
Package Level 3 Units:	14400 piece
Product Packing Type:	Box

