

## SMD female connector, shielded - FP 0,8/ 52-FV-SH 4,85 - 1043713

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Shielded SMD female connector, Nominal current at 20 °C: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, mounting: SMD soldering

The figure shows a 12-pos. version with 12 contacts

### Your advantages

- ✓ Gold-plated contacts ensure transfer quality remains stable over the long term
- ✓ Reliable mechanical and electrical connections, thanks to the double-sided ScaleX contact system
- ✓ Robustness: ScaleX technology for high tolerance compensation and protection of contacts
- ✓ Flexible device design: various numbers of positions, designs, and stack heights with high wipe lengths



### Key Commercial Data

Packing unit	500 pc
Minimum order quantity	500 pc
GTIN	
GTIN	4055626612393
Weight per Piece (excluding packing)	2.260 g
Custom tariff number	85366990
Note	Made to Order (non-returnable)

### Technical data

#### Item properties

Brief article description	SMD female connector, shielded
Plug-in system	FINEPITCH 0,8 mm shielded
Type of contact	Female connector
Electrical characteristic	shielded
Range of articles	FP 0,8/...-FV-SH 4,85
Pitch	0.8 mm
Number of positions	52

# SMD female connector, shielded - FP 0,8/ 52-FV-SH 4,85 - 1043713

## Technical data

### Item properties

Mounting type	SMD soldering
Number of levels	2
Number of potentials	52

### Electrical data

Nominal current at 20 °C	1.7 A (52-pos.)
Test voltage	500 V AC IEC 60512-4-1:2003

### Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/ JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Selective coating
Metal surface contact area (top layer)	Gold (Au)
Metal surface contact area (middle layer)	Nickel (Ni),
Metal surface soldering area (top layer)	Tin (Sn)
Metal surface soldering area (middle layer)	Nickel (Ni)

### Material data - housing

Insulating material	LCP
Insulating material group	IIIa
CTI according to IEC 60112	150
Flammability rating according to UL 94	V0

### Dimensions for the product

Length [ l ]	7.1 mm
Width [ w ]	25.58 mm
Height [ h ]	5.45 mm
Pitch	0.8 mm
Height (without solder pin)	4.85 mm
Coplanarity	≤ 0.1 mm

### Dimensions for the application

Contact cover	0.8 mm
Overlap length	1.5 mm
Medium offset	± 0.7 mm in longitudinal and transverse direction
Angular tolerance	± 2 ° in longitudinal direction
	± 4 ° in transverse direction
Stack height	6 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-MV-SH 1,15)
	7.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-MV-SH 2,65)

### Packaging information

Type of packaging	44 mm wide tape
-------------------	-----------------

## SMD female connector, shielded - FP 0,8/ 52-FV-SH 4,85 - 1043713

### Technical data

#### Packaging information

Pieces per package	500
Denomination packing units	Pcs.
[W] tape width	44 mm
[A] coil diameter	330 mm
[W2] coil overall dimension	50 mm
Outer packaging type	Transparent-Bag

#### Data transmission

Caption	Type: FP 0,8/...-FV-SH 4,85 with FP 0,8/...-MV-SH 1,15 Differential pair – 7.5 mm high
Caption	Type: FP 0,8/...-FV-SH 4,85 with FP 0,8/...-MV-SH 1,15 Differential pair – 7.5 mm high

#### Processing notes

Process	Reflow soldering
Specification	Following IPC/JEDEC J-STD-020E:2014-12
Moisture Sensitive Level	MSL 1
Classification temperature T <sub>c</sub>	260 °C

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-55 °C ... 125 °C


#### Air clearances and creepage distances

Air clearances and creepage distances	min. 0.25 mm
---------------------------------------	--------------

### Drawings

# SMD female connector, shielded - FP 0,8/ 52-FV-SH 4,85 - 1043713

Schematic diagram



## Classifications

eCl@ss

eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 5.0	EC002637
ETIM 6.0	EC002637
ETIM 7.0	EC002637

## Approvals

Approvals

Approvals

cULus Recognized

## SMD female connector, shielded - FP 0,8/ 52-FV-SH 4,85 - 1043713

### Approvals

Ex Approvals

---

### Approval details

cULus Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> E118976-20190703

### Accessories

#### Additional products

SMD male connector, shielded - FP 0,8/ 52-MV-SH 2,65 - 1043756



shielded SMD male connector, Nominal current at 20 °C: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold

---

SMD male connector, shielded - FP 0,8/ 52-MV-SH 1,15 - 1043789



shielded SMD male connector, Nominal current at 20 °C: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, mounting: SMD soldering

---

SMD male connector, shielded - FP 0,8/ 52-MH-SH - 1043793



shielded SMD male connector, Nominal current at 20 °C: 1.4 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold