Pluggable PCB Connector Plug, 3.5mm Pitch


multicomp PRO




Specifications

Current Rating	: 10 Amperes, 300V AC
Min. Insulation withstand Voltage	: 2,000V AC
Insulation resistance	: >2,000MΩ 500V DC
Pitch	: 3.5mm
Poles	: 2 to 12 Poles
Housing Material	: PA 66
Cage Clamp	: Brass, Ni Plated
Contact	: Phosphor Bronze, Tin Plated
Screw Thread	: M2.0, Steel, Zinc Plated
Wire Size	: 16 to 26AWG
Tightening Torque, Max.	: 3lb-inch
Operating Temperature	: -40°C to +105°C
Technical Data	
Nominal Current IN	: 8A
Nominal Cross Section	: 1.5mm ²

Diagram





Max. Load Current

Insulating Material

Dimensions : Millimetres (Inches)

Part Number Table

:8A

: PA

Description	Poles	Part Number
	2	MC000056
	3	MC000057
	4	MC000058
Diug 2 Emm Straight 104	5	MC000059
Plug 3.5mm Straight 10A	6	MC000060
	8	MC000061
	10	MC000062
	12	MC000063

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

