

PRODUCT-DETAILS

# SAMHL63/10M

## 63MM GALV CORE ANTI MICRO COND 10M



### General Information

Extended Product Type	SAMHL63/10M
Product ID	7TCA296030R0452
EAN	5020963801617
Catalog Description	63MM GALV CORE ANTI MICRO COND 10M
Long Description	Liquidtight, Anti-Microbial Conduit, Conduit Size - Metric 63 Millimeters / US Trade Size 2 Inch, Outside Diameter 59.7mm, Inside Diameter 51.6mm, Static Bend Radius 345mm, IP40-IP69 Rating, Galvanised Steel Core with Thermoplastic Jacket, Reel Length 10 Meters, White

### Ordering

EAN	5020963801617
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	40.79 lb 18.499 kg
--------------------	-----------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

---

### Additional Information

Application	Suitable for indoor splash zone areas or food processing equipment
Brand / Label	Adaptaflex
Color	White
Flexibility	High
Inside Diameter	51.6 mm
Material	Galvanised Steel Core, String Packed and Thermoplastic Jacket
Nominal Size	63 mm
Number of Batteries	0
Outside Diameter	59.7 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Anti-Microbial Conduit
Radius	345 mm
UPC	786210213071

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SAMHL63/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SAMHL63/10M

---

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

