

C.A 6255

10 A MICRO-OHMMETER



- Optimized current generator on inductive objects
- Measurement up to 2,500 Ω , resolution 0.1 $\mu\Omega$
- Automatic compensation of stray voltages
- Calculation of R at a reference temperature -Pt100 Ω probe
- Automatic discharge after test
- Programmable alarms
- Storage of up to 1,500 measurements
- Communication with a PC















With its intuitive use, the C.A 6255 "highperformance" micro-ohmmeter is ideal for measuring very low resistance values with very high accuracy: 0.1 $\mu\Omega$.



INTERFACE for connection to a PC

Wide measurement range with 7 calibres accessible using the rotary switch

Activation / deactivation of the temperature compensation function

Storage of up to 1,500 measurements / rereading of data

Choice of measurement mode / Selection of the metal for temperature compensation calculation

probes are available:


Kelvin 10 A clamps

Two models of retractable 10 A Kelvin test

"pistol-type"

test probes

DataView® software platform for data processing



The MOT module of DataView® can be used to:

- Configure instruments connected to a PC
- Recover the measurement data stored in the instrument
- Back up the measurement files



3 measurement modes



NON-INDUCTIVE MODE

for measurements on resistors with a time constant of a few ms (contacts, metallization, etc.)



INDUCTIVE MODE

for measurements on inductive components (transformers, motors, etc.)



NON-INDUCTIVE MODE with AUTOMATIC trigger

- for measurements on resistors without a time constant
- for repetitive measurements in production, helping to gain considerable time

Functions



TEMPERATURE COMPENSATION

The value of a resistance varies according to the temperature. For reliable supervision allowing the comparison of measurements which are comparable because they were made in the same conditions, it is a good idea always to express a measurement in terms of a given reference temperature. You can perform this calculation by simply pressing a key.



PROGRAMMABLE ALARMS

Because an audio signal is sometimes all you need to interpret and assess a measurement, it is possible to activate a high and/or low alarm. If it is overshot, a buzzer sounds (adjustable volume).



EXTENDED MEASUREMENT

The C.A 6255 is equipped with an internal memory capable of storing 1,500 measurements. They are memorized with two indices, OBJ (object) and TEST (test), which store the results in an ordered manner.

Numerous applications

 Measurements on windings (e.g. transformer) without overheating of the C.A 6255




- Surface finish and metallization
- Chassis-earth continuity/bonding test



Quality of the contacts (switches, relays)



- Resistance of cables
- ► Heating of motors and transformers
- Verification of mechanical linkage



4-wire measurement method							
Calibre	5.0000 mΩ	25.000 mΩ	250.00 mΩ	2500.0 mΩ	25.000 Ω	250.00 Ω	2500.0 Ω
Resolution	0.1 μΩ	1 μΩ	10 μΩ	0.1 mΩ	1 m Ω	10 mΩ	100 mΩ
1-year accuracy	0.05 % + 1 μΩ	0.05 % + 3 μΩ	0.05 % + 30 μΩ	0.05 % + 0,3 mΩ	0.05 % + 3 mΩ	0.05 % + 30 mΩ	0.05 % + 300 mΩ
Measurement current	10 A	10 A	10 A	1 A	100 mA	10 mA	1 mA
Voltage drop	50 mV	250 mV	2,500 mV	2,500 mV	2,500 mV	2,500 mV	2,500 mV
Measurement modes	Inductive, non-inductive, non-inductive with automatic trigger						
Temperature compensation	By temperature sensor or manual						
Data storage	1,500 measurements						
Communication output	RS 232 link						
Power supply	NiMH rechargeable battery						

270 x 250 x 180 mm / approx. 4 kg

Accessories

Dimensions / Weight

Double test probes and Kelvin clamps for micro-ohmmeters				
	10 A Kelvin clamps (set of 2) • L = 3 m	Spade lug	P01101794	
	Double 10 A "pistol" test probe (set of 2) • L = 3.15 m • Ø 2 mm test probes • Test-probe spacing: 3.5 mm	Spade lug and 4 mm banana	P01103065	
	Double 10 A pivoting test probe (set of 2) • L = 3.15 m • Ø 3 mm test probes • Travel of probes: 10 mm	Spade lug and 4 mm banana	P01103063	
	1 A Mini Kelvin clamps (set of 2)	Spade lug	P01101783	
	Double 1 A test probe (set of 2) • L = 2.85 m	Spade lug and 4 mm banana	P01102056	
Temperature				
TEMP 0 Interes	Pt 100 probe		P01102013	



State at delivery

Delivered with a bag containing:

- 1 set of cables 3 m long terminated by Kelvin clamps
- 1 Euro mains power lead 2 m long
- 9 user's manuals (1 per language)
- 9 simplified user's manuals (1 per language)
- MOT (Micro-Ohmmeter Transfer) data transfer software on CD-ROM
- 1 x RS232 communication cable

Reference to order

C.A 6255 P01143221

FRANCE

Chauvin Arnoux

190, rue Championnet 75876 PARIS Cedex 18 Tel: +33 1 44 85 44 38 Fax: +33 1 46 27 95 59 export@chauvin-arnoux.fr www.chauvin-arnoux.com

UNITED KINGDOM Chauvin Arnoux Ltd

Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk Dewsbury, West Yorkshire - WF12 7TH Tel: +44 1924 460 494 Fax: +44 1924 455 328 info@chauvin-arnoux.co.uk www.chauvin-arnoux.com

Middle East Chauvin Arnoux Middle East

P.O. BOX 60-154 1241 2020 JAL EL DIB - LEBANON Tel: +961 1 890 425 Fax: +961 1 890 424 camie@chauvin-arnoux.com www.chauvin-arnoux.com

