

## Flat gasket - WP-FS IP68 M20 - 3241162

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Flat gasket, height: 1.8 mm, diameter: 29 mm, color: black




### Your advantages

- The Perbunan flat sealing rings are used to seal protective hose screw connections on uneven surfaces.
- Up to IP68 protection is achieved.



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 50 pc   |
| Minimum order quantity               | 50 pc   |
| GTIN                                 | <br>4 046356 785686 |
| GTIN                                 | 4046356785686   |
| Weight per Piece (excluding packing) | 0.910 g   |
| Custom tariff number                 | 40169300  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### Dimensions

|                        |        |
|------------------------|--------|
| Height (c)             | 1.8 mm |
| Diameter               | 29 mm  |
| Inner diameter (f)     | 20 mm  |
| Material thickness (g) | 1.8 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -20 °C ... 120 °C |
| Degree of protection            | IP68              |

#### General

# Flat gasket - WP-FS IP68 M20 - 3241162

## Technical data

### General

|            |                                |
|------------|--------------------------------|
| Color      | black                          |
| Components | free from silicone and halogen |
| Material   | Perbunan                       |

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27430319 |
| eCl@ss 4.0    | 27141200 |
| eCl@ss 4.1    | 27141200 |
| eCl@ss 5.0    | 21132000 |
| eCl@ss 5.1    | 21132000 |
| eCl@ss 6.0    | 21132000 |
| eCl@ss 7.0    | 27439218 |
| eCl@ss 8.0    | 27439218 |
| eCl@ss 9.0    | 27430319 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000519 |
| ETIM 4.0 | EC000519 |
| ETIM 5.0 | EC001181 |
| ETIM 6.0 | EC001181 |
| ETIM 7.0 | EC001181 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39131608 |
| UNSPSC 18.0   | 39131608 |
| UNSPSC 19.0   | 39131608 |
| UNSPSC 20.0   | 39131608 |
| UNSPSC 21.0   | 39131608 |