

Mandatory sign - US-PML-M100 (D50) - 1014176

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Mandatory sign, Card, blue/white, unlabeled, can be labeled with: THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: Blank, mounting type: adhesive, diameter: 50 mm, lettering field size: d: 50 mm, Number of individual labels: 4




Your advantages

- UniSheet - stick-on mandatory signs, color preprinted, without symbol
- Suitable for indoor and outdoor use
- The mandatory signs conform to the ISO 7010 international standard
- Highly flexible, plasticized PVC labels which are ideal for uneven surfaces



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 786447
GTIN	4046356786447
Weight per Piece (excluding packing)	5.370 g
Custom tariff number	39199080
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width (a)	0 mm
Height (c)	0 mm
Diameter	50.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 8 °C

Mandatory sign - US-PML-M100 (D50) - 1014176

Technical data

Ambient conditions

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

General

Color	blue/white
Type	Round
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	Blank
Number of individual labels	4
Adhesive	Acrylic
Printability	Thermal transfer
Device	5148888 THERMOMARK PRIME
Ink ribbon	0803376 TMP-RIBBON 110 WH 100
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Procedure	A
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

	Reaction mass of DOTE and MOTE
--	--------------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	40200201
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100

Mandatory sign - US-PML-M100 (D50) - 1014176

Classifications

eCl@ss

eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200201
eCl@ss 9.0	40200201

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110 WH 100 - 0804661



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing the material off the roll product groups: EML..., EMLP ..., EMLF..., PML-M..., PML-T... and US material product groups: US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-WMT..., US-WMTB ..., US-PML-M..., US-EMLF..., width: 110 mm, color: white

Mandatory sign - US-PML-M100 (D50) - 1014176

Accessories

Ink ribbon cartridge - TMP-RIBBON 110 WH 100 - 0803376



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: white

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards