


**PHYSICAL DIMENSIONS**



Cap: G13

**PRODUCT FEATURES**

- fluorescent lamp with 26 mm diameter
- available light colours: *Skywhite* (880), *Cool Daylight* (865), *Daylight* (850); *Cool White* (840), *White* (835), *Warm White* (830), *INTERNA* (827)
- reduced power consumption
- very good colour rendering ( $R_a$  80 ... 89)

**Technical Data**

Frequency	(Hz)	:	50 Hz-Operation
Lamp wattage	(W)	:	36
Nominal current (CCG-operation) uncompensated	(A)	:	0,43
Lamp arc voltage UL after switch-on ( $\pm 10\%$ )	(V)	:	103
Resistance / Impedance Z (for CCG)	( $\Omega$ )	:	240
System power – CCG-operation	(W)	:	depends on EEI-class of CCG
Pre-heat current IEC 81	(mA)	:	650
Luminance	(cd/cm <sup>2</sup> )	:	1,2
Compensation capacitor (power factor $\approx 1$ for CCG)	( $\mu$ F)	:	4,5
Row capacitor for CCG duo wiring	( $\mu$ F/Vc)	:	3,4/450

**Life Time\***

Average life time (50% failure rate)	(h)	:	15000 (CCG inductive) / 20000 (ECG pre-heat start)
Service life time (80% lum. flux from initial 100h value)	(h)	:	12000 (CCG inductive) / 18000 (ECG pre-heat start)

**PHOTOMETRICAL DATA**

Labelling in brand OSRAM	Rated luminous flux** (lm)	Colour rendering index ( $R_a$ )	Colour temperature (K)
L 36W/880	2900	80...89	8000
L 36W/865	3250	80...89	6500
L 36W/850	3300	80...89	5000
L 36W/840	3350	80...89	4000
L 36W/835	3350	80...89	3500
L 36W/830	3350	80...89	3000
L 36W/827	3350	80...89	2700

\*\* at 50 Hz operation and aged 100h; 25°C ambient temperature

**Note:** \*Measurement in accordance with EN 60081, annex C.  
 The lamps meet EN 60081 and EN 61195 requirements.  
 Starter and ballasts have to meet EN 60155 and EN 60921 requirements.

