


Capacitor, tantalum, 15 uF, 10% Tol, 10V@85C, C



Dimensions (mm)

Specifications

ID	Dimension	Tolerance	Application:	General Purpose
L	6.00	+/-0.30	Capacitance:	15 uF
W	3.20	+/-0.30	Tolerance:	10%
H	2.50	+/-0.30	Voltage DC @ 85C:	10V
K	1.40	+/-0.20	Voltage DC @ 105C:	8.2V
F	2.20	+/-0.10	Voltage DC @ 125C:	6.3V
S	1.30	+/-0.30	Temperature Range:	-55/+125C
B	0.50	+/-0.15	Size Code:	C
X	0.10	ref	Footprint:	6032
P	0.90	ref	Body Type:	Molded Chip
R	1.00	ref	Packaging:	T&R
T	0.13	ref	Package Quantity:	750
A	2.50	ref	Termination Type:	Tin (Pb free)
G	2.80	ref	Leakage Current:	1.5 uA
E	2.40	ref	Dissipation Factor:	6%
			Impedance @ 100kHz:	2 Ohm