


Capacitor, tantalum, 470 uF, 10% Tol, 10V@85C, E



**Dimensions (mm)**

**Specifications**

ID	Dimension	Tolerance	Application:	Low ESR
L	7.30	+/-0.30	Capacitance:	470 uF
W	4.30	+/-0.30	Tolerance:	10%
H	4.10	+/-0.30	Voltage DC @ 85C:	10V
K	1.80	nom	Voltage DC @ 105C:	8.2V
F	2.40	+/-0.10	Voltage DC @ 125C:	6.3V
S	1.30	+/-0.30	Temperature Range:	-55/+125C
			Size Code:	E
			Footprint:	7343
			Body Type:	Molded Chip
			Packaging:	T&R
			Package Quantity:	400
			Termination Type:	Tin (Pb free)
			Leakage Current:	47 uA
			Dissipation Factor:	15%
			ESR:	100 mOhm
			Ripple @ 25C:	1.28 A
			Ripple @ 85C:	1.152 A
			Ripple @ 125C:	0.512 A