Data Sheet



Coaxial Cable Connector 11_TNC-50-7-5/133_U

Description

Straight cable plug

Interface standards

IEC 60169-17 MIL-STD-348A/313 CECC 22200

Technical Data

Electrical Data

 $\begin{array}{ll} \mbox{Impedance} & \mbox{50} \ \Omega \\ \mbox{Interface frequency max.} & \mbox{11 GHz} \end{array}$

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0234 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)

-65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00007798
Assembly instruction DOC-0000179092

Ordering Information

Single package 11_TNC-50-7-5/133_UE

Additional Information

Suitable cables RG_213_/U, GX_07272, G_07262, G 07272, RADOX_RF_213

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.