# **Data Sheet**



# Coaxial Cable Connector 21\_TNC-50-4-16/133\_N

# **Description**

Straight cable jack

Interface standards
IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



4 to 6 GHz

25.5 dB

# **Technical Data**

**Electrical Data** 

 $\begin{array}{lll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 11 \ \text{GHz} \\ \text{Frequency range} & \text{DC to 2 GHz} \\ \text{Return loss} & 30 \ \text{dB} \\ \end{array}$ 

**Mechanical Data** 

Centre contact plugged
Outer contact crimped
Weight 0.01412 kg

**Environmental Data** 

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

#### **Material Data**

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

2 to 4 GHz

27.4 dB

# **Related Documents**

Outline drawing DOU-00166940
Assembly instruction DOC-0000347534

# Ordering Information

Single package 21\_TNC-50-4-16/133\_NE

### **Additional Information**

Suitable cables SX\_04172\_B-60, SPUMA\_240

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.