

Mains plug - PLD E 400-PS/1AC/24DC/30W - 2702436

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plug-in power supply unit for class 400 LED enclosure lights, including country-specific plug adapters for Europe, Great Britain, USA and Australia; max. output voltage 30 W




Product Description

The plug-in power supply unit is intended for supplying power to class 400 LED enclosure lights. A power supply unit and four country-specific plug adapters, e.g., for Europe, Great Britain, the USA, and Australia, are supplied as standard. By connecting the country-specific plug adapter to the power supply unit, you can adapt the plug-in power supply unit to the installation location.

Your advantages

- ✓ High efficiency
- ✓ Minimum standby power dissipation ≤ 0.1 W
- ✓ IP42-tested interchangeable adapter system

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 184678
GTIN	4055626184678
Weight per Piece (excluding packing)	222.220 g
Custom tariff number	85044082
Country of origin	Germany

Technical data

Dimensions

Width	55 mm
Height	90 mm
Depth	34 mm

Ambient conditions

Degree of protection	IP42
Ambient temperature (operation)	0 °C ... 40 °C (at maximum load)

Mains plug - PLD E 400-PS/1AC/24DC/30W - 2702436

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Installation height	2000 m

Input data

Nominal input voltage range	100 V AC ... 240 V AC ±10 %
AC frequency range	50 Hz ... 60 Hz
Maximum inrush current	650 mA
Discharge current to PE	max. 250 µA
Type of protection	Surge protection

Output data

Nominal output voltage	24 V DC ±5 %
Residual ripple	120 mV _{pp}
Output power	30 W
Typical response time	max. 2 s
Maximum power dissipation in no-load condition	max. 0.1 W
Type of protection	Surge protection

Connection data, output

Cable end connection	M8 socket (Snap-in)
Connecting cable length	2 m

General

Efficiency	≥ 86.95 %
Protection class	II
Degree of protection	IP42
Can be used as typical for the country	Australia
	Belgium
	Brazil
	China
	Denmark
	Germany
	Finland
	France
	Greece
	Great Britain
	India
	Ireland
	Italy
	Japan
	Canada
	Luxembourg

Mains plug - PLD E 400-PS/1AC/24DC/30W - 2702436

Technical data

General

	Mexico
	Netherlands
	Norway
	Austria
	Poland
	Portugal
	Russia
	Sweden
	Switzerland
	Spain
	Singapore
	Turkey
	USA

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---


Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 25;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Mains plug - PLD E 400-PS/1AC/24DC/30W - 2702436

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27110700
eCl@ss 4.1	27110700
eCl@ss 5.0	27119000
eCl@ss 5.1	27119000
eCl@ss 6.0	27119200
eCl@ss 7.0	27119290
eCl@ss 8.0	27119290
eCl@ss 9.0	27119290

ETIM

ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC002558

Mains plug - PLD E 400-PS/1AC/24DC/30W - 2702436

Classifications

ETIM

ETIM 6.0	EC002558
ETIM 7.0	EC002558

UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410
UNSPSC 18.0	39111541
UNSPSC 19.0	39111541
UNSPSC 20.0	39111541
UNSPSC 21.0	39111541

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 214596
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 214596
------------	--	---	---------------

cULus Listed			
--------------	--	--	--