

Wireless module - FL EPA 2 - 1005955

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Combined Ethernet wireless module with Bluetooth and Wi-Fi, internal antenna, Wi-Fi: AP and client, 2.4 and 5 GHz, Bluetooth: 2.1+EDR/4.0, PAN up to 7 connections, IP65, 9 ... 30 V DC, M12 connection, WEB, AT commands and mode button

Your advantages

- Integrated antenna
- Protocol-transparent communication on Layer 2
- IP65 protection class
- Combined wireless module for WLAN and Bluetooth



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 476568
GTIN	4055626476568
Weight per Piece (excluding packing)	166.000 g
Custom tariff number	85176200
Country of origin	Sweden

Technical data

Dimensions

Width	67.8 mm
Height	92.7 mm
Depth	33.2 mm
Note on dimensions	Without M12 connections

Ambient conditions

Ambient temperature (operation)	-40 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 93 % (non-condensing)
Permissible humidity (storage/transport)	non-condensing

Wireless module - FL EPA 2 - 1005955

Technical data

Ambient conditions

Degree of protection	IP65
----------------------	------

Ethernet interface

Interface	Ethernet
Number	1
Connection method	M 12 connectors (D-coded, female)
Interface	10/100 Mbps Ethernet
Number of interfaces	1
Connection method	M 12 connectors (D-coded, female)
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)

Wireless interface

Designation	Bluetooth / WLAN
Wireless standard	Bluetooth 2.1 + EDR
	IEEE 802.11
	b
	g
	a
	n
Antenna connection method	(Internal)
Frequency range	2.402 GHz ... 2.48 GHz (Bluetooth)
	2.4095 GHz ... 2.4645 GHz (WLAN)
	5.17 GHz ... 5.25 GHz (WLAN-AP)
	5.17 GHz ... 5.71 GHz (WLAN-Client)
Frequency band	2.4 GHz
	5 GHz
Transmission power	max. 16 dBm (Bluetooth: 10 dBm)
Number of wireless interfaces	1 IEEE 802.11 a/b/g/n, Bluetooth 2.1+EDR, Bluetooth LE 4.0
Wireless modules that can be connected	7 (BT 2.1+EDR, NAP-Mode)

Wireless card

Number	1
Assembly instructions	Permanently installed

Antenna

Assembly instructions	Internal antenna
-----------------------	------------------

Power supply for module electronics

Connection technology	M12 connector
Connection method	M12 connector (A-coded, male)

Wireless module - FL EPA 2 - 1005955

Technical data

Power supply for module electronics

Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Supply current	typ. 54 mA (at 24 V DC)
Current consumption	max. 190 mA (at 9 V DC)

Functions

Operating modes	Access point/client adapter for WLAN and Bluetooth
Configuration	Web interface, MODE button, AT commands (TCP/IP), SSC
Security	802.11i
	WPA PSK (preshared key)
	WPA2
	AES
	TKIP
	PIN
	Non-discoverable

Digital inputs

Number of inputs	1
------------------	---

General

Mounting type	Wall mounting
Net weight	166 g
Wireless licenses	Europe, USA, Canada, additional countries in the e-shop
	RED (Radio Equipment Directive)
	FCC 47 CFR part 15, subpart B
Wireless licences	Belgium
	Bulgaria
	Denmark
	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Iceland
	Italy
	Canada
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg

Wireless module - FL EPA 2 - 1005955

Technical data

General

	Malta
	Netherlands
	Norway
	Austria
	Poland
	Portugal
	Romania
	Sweden
	Switzerland
	Slovakia
	Slovenia
	Spain
	Czech Republic
	Hungary
	USA
	Cyprus (rep.)
	Japan
Mounting type	Wall mounting

Standards and Regulations

Mechanical tests	Shock in acc. with EN 60068-2-27/IEC 60068-2-27 3g, 11 ms half-sine shock pulse
	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6 5 - 8.4 Hz= ±3.5 mm; 8.4 - 40.7 Hz = 1g; 40.7 - 57Hz= ±0.15 mm; 57 - 500 Hz= 2g
Standards/regulations	EN 61000-4-2
	EN 61000-4-3
	EN 61000-4-4
	EN 61000-4-5
	EN 55022
	EN 61000-4-6

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215

Wireless module - FL EPA 2 - 1005955

Classifications

eCl@ss

eCl@ss 5.1	27250501
eCl@ss 6.0	19170100
eCl@ss 7.0	19170101
eCl@ss 8.0	19170101
eCl@ss 9.0	19170101

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC000515
ETIM 5.0	EC000515
ETIM 6.0	EC000515
ETIM 7.0	EC000515

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	43201404
UNSPSC 18.0	43201404
UNSPSC 19.0	43201404
UNSPSC 20.0	43201404
UNSPSC 21.0	43201404

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

Wireless module - FL EPA 2 - 1005955

Approvals

cUL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 238705

cULus Listed



Accessories

Accessories

Assembly adapter

Assembly adapters - FL EPA WMS - 2701134



Set for mounting devices with EPA design to wall or mast, including mast clips for a diameter of 25 - 85 mm, can be moved on two axes for optimum alignment, stainless steel

Data cable preassembled

Bus system cable - SAC-4P-M12MSD/ 2,0-931 - 1569391



Bus system cable, Ethernet CAT5 (100 Mbps), 4-position, PUR halogen-free, water blue RAL 5021, shielded, Plug straight M12, D-coded, on free cable end, cable length: 2 m

Bus system cable - SAC-4P-M12MSD/ 5,0-931 - 1569401



Bus system cable, Ethernet CAT5 (100 Mbps), 4-position, PUR halogen-free, water blue RAL 5021, shielded, Plug straight M12, D-coded, on free cable end, cable length: 5 m

Network cable - NBC-MSD/ 1,0-93E/R4AC SCO - 1407360



Network cable, Ethernet CAT5 (100 Mbps), 4-position, PUR, water blue RAL 5021, shielded, Plug straight M12 SPEEDCON / IP67, coding: D, on Plug straight RJ45 / IP20, cable length: 1 m

Wireless module - FL EPA 2 - 1005955

Accessories

Network cable - NBC-MSD/ 2,0-93E/R4AC SCO - 1407361



Network cable, Ethernet CAT5 (100 Mbps), 4-position, PUR, water blue RAL 5021, shielded, Plug straight M12 SPEEDCON / IP67, coding: D, on Plug straight RJ45 / IP20, cable length: 2 m

Network cable - NBC-MSD/ 5,0-93E/R4AC SCO - 1407362



Network cable, Ethernet CAT5 (100 Mbps), 4-position, PUR, water blue RAL 5021, shielded, Plug straight M12 SPEEDCON / IP67, coding: D, on Plug straight RJ45 / IP20, cable length: 5 m

Data plug

RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: PA, connection method: IDC fast connection, connection cross section: AWG 26- 23, cable outlet: straight, color: traffic grey A RAL 7042

Mounting rail adapter

DIN rail adapter - FL EPA RMS - 2701133

Set for mounting devices with EPA design on a DIN rail



Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 2,0-PUR/M12FS - 1533576



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, A-coded, cable length: 2 m

Wireless module - FL EPA 2 - 1005955

Accessories

Sensor/actuator cable - SAC-4P- 3,0-PUR/M12FS - 1668111



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, A-coded, cable length: 3 m

Sensor/actuator cable - SAC-4P- 5,0-PUR/M12FS - 1668124



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, A-coded, cable length: 5 m

Sensor/actuator cable - SAC-4P-10,0-PUR/M12FS - 1683002



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, A-coded, cable length: 10 m
