

Within Series Adaptor 43_N-50-0-1/133_N

Description

T-adaptor, 2 jacks, 1 plug
N jack (female) / N plug (male)

Interface standard
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 11 GHz

Mechanical Data

Number of matings 500
Weight 0.0803 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing DOU-00013557

Ordering Information

Single package 43_N-50-0-1/133_NE