

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2119420002](#)  
**Status:** **Active**  
**Overview:** Coeur CST High-Current Interconnect System  
**Description:** Coeur CST High-Current 6.00mm Receptacle Crimp Housing, Dual Row, 2 Circuits, Keying Option A, Red

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2119420000-PK-000 (PDF)</a>
<a href="#">Product Specification 2119410000-PS-000 (PDF)</a>	<a href="#">Test Summary 2119410000-TS-000 (PDF)</a>
<a href="#">Application Specification 2119410000-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">211942</a>
Application	Power, Wire-to-Board
Overview	<a href="#">Coeur CST High-Current Interconnect System</a>
Product Name	Coeur CST
UPC	191130961375


**Physical**

Circuits (maximum)	2
Color - Resin	Red
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	18.323/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	19.06mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2119410000-AS-000
Packaging Specification	2119420000-PK-000
Product Specification	2119410000-PS-000
Sales Drawing	2119420000-SD-000
Test Summary	2119410000-TS-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[211942](#) Series

**Mates With**

6.00mm Male Header [211937](#)

**Use With**

6.00mm Female Crimp Socket [204608](#)  
<br> 6.00mm Terminal Retention Housing  
[211888](#)