

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200680229](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Solid Body Splitter, 1 x 4-Pole Male to 2 x 4-Pole Females, Grey PVC Overmold

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|--|
| Product Family | Industrial Tees and Splitters |
| Series | 120068 |
| IP Rating | IP67 |
| Overview | Brad Micro-Change (M12) Connectors |
| Product Name | Micro-Change (M12) |
| Type | Splitter - Solid Body |
| UPC | 78678825650 |

Physical

| | |
|-------------------------------|-------------------------|
| Drop Connector | Micro-Change (M12) |
| Drop Gender | Male |
| Keyway | Single |
| LED Indicator | No |
| Left Trunk Connector | Micro-Change (M12) |
| Left Trunk Gender | Female |
| Leg 1 Length | N/A |
| Leg 2 Length | N/A |
| Material - Cable Jacket | N/A |
| Material - Connector Body | PVC |
| Material - Coupling Nut | Black Epoxy Coated Zinc |
| Net Weight | 93.031/g |
| Poles | 3 Female/4 Male |
| Right Trunk Connector | Micro-Change (M12) |
| Right Trunk Gender | Female |
| Temperature Range - Operating | -20°C to +105°C |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 24V DC |

Material Info

| | |
|--------------------|-------|
| Engineering Number | 81590 |
|--------------------|-------|

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | SD-120068-034 |
|---------------|---------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[120068 Series](#)