LEAD-FREE COMPATIBLE COMPONENT

# Conductive Polymer, Miniature, Undertab Solid Electrolytic Chip Capacitors



#### **FEATURES**

- · Conductive polymer electrode
- Benign failure mode under recommended use
- Compliant to the RoHS2 directive 2011/65/EU
- SMD facedown
- Small and low profile
- High volumetric efficiency

# **APPLICATIONS**

- Smartphone

- · Portable game
- · Bulk decoupling of SoC

#### Tablet PC


Wireless module (System on chip)

#### **CASE DIMENSIONS:**


## millimeters (inches)

Code	EIA Code	EIA Metric	L	W <sub>1</sub>	W <sub>2</sub>	Н	S <sub>1</sub>	S <sub>2</sub>
М	0603	1608-09	$1.60^{+0.20}_{-0.10}$ $(0.063^{+0.008}_{-0.004})$	0.85 +0.20 -0.10 (0.033 +0.008 -0.004)	0.65±0.10 (0.026±0.004)	0.80±0.10*1 (0.031±0.004)	0.50±0.10 (0.020±0.004)	0.60±0.10 (0.024±0.004)
S	0805	2012-09	2.00 <sup>+0.20</sup> <sub>-0.10</sub> (0.079 <sup>+0.008</sup> <sub>-0.004</sub> )	1.25 +0.20 (0.049 +0.008 )	0.90±0.10 (0.035±0.004)	0.80±0.10 (0.031±0.004)	0.50±0.10 (0.020±0.004)	1.00±0.10 (0.039±0.004)
U	0402	1106-06	1.10±0.05 (0.043±0.002)	0.60±0.05 (0.024±0.002)	0.35±0.05 (0.014±0.002)	0.55±0.05 (0.022±0.002)	0.30±0.05 (0.012±0.002)	0.50±0.05 (0.020±0.002)

<sup>\*1</sup> F380J476MMAAXE: 1.0mm Max.



# **HOW TO ORDER**



225 Capacitance Code

pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)



**Tolerance** M=±20%



table above

# **Packaging**



#### **Special Code** AXE = Rated temperature 60°C and H dimension 1.0mm Max.

AXEH3 = Rated temperature 60°C and H dimension 1.0mm Max., Low ESR

LZT = Rated temperature 60°C

LZTH1 = Rated temperature 60°C, Low ESR

AH1, AH2, AH3 = Low ESR

#### **TECHNICAL SPECIFICATIONS**

Category Temperature Range:	-55 to +105°C
Rated Range:	+85°C or +60°C (*2)
Capacitance Tolerance:	±20% at 120Hz
Dissipation Factor:	Refer to next page (120Hz)
ESR 100kHz:	Refer to next page (120Hz)
Leaking Current:	Refer to next page
	At 20°C after application of rated voltage for 5 minutes
	Provided that:
	After 5 minute's application of rated voltage, leakage current at 105°C
	10 times or less than 20°C specified value.
Termination Finish:	M, S case: Gold Plating (standard), U case: Sn-3.5Ag Plating (standard)

<sup>\*2</sup> LZT and AXE: Rated temperature +60°C, Surge and Endurance test temperature +60°C





# Conductive Polymer, Miniature, Undertab Solid Electrolytic Chip Capacitors

# **CAPACITANCE AND RATED VOLTAGE RANGE** (LETTER DENOTES CASE SIZE)

Capacitance		Rated Voltage						
μF	Code	4V (0G)	6.3V (0J)	10V (1A)	25V (1E)	Code		
1.0	105		U			Α		
2.2	225			M	М	J		
4.7	475		U	M/S	S	S		
10	106		M/M(AH1,AH2)/S/U	M/M(AH1)		а		
22	226		M/M(AH3,AH1)/S/S(AH1)	M*4/S		j		
33	336		M**/S	S**		n		
47	476		M*4/M*4(H3)/S/S(AH1)	S**		s		
68	686		S**			w		
100	107	S**	S**/S**(H1)			Α		

Please contact to your local AVX sales office when these series are being designed in your application.

# THE CORRELATIONS AMONG **RATED VOLTAGE, SURGE VOLTAGE AND DERATED VOLTAGE**

	F38 (Standard)			
Rated Voltage (V) ≤85°C	6.3	10	25	
85°C Surge Voltage (V)	8	13	32	
105°C Derated Voltage (V)	5	8	20	

	F38-LZT, F38-AXE			
Rated Voltage (V) ≤60°C	4	6.3	10	
60°C Surge Voltage (V)	5.2	8	13	
85°C Derated Voltage (V)	2.8	4.5	7.2	
105°C Derated Voltage (V)	2	3.3	5	

## **RATINGS & PART NUMBER REFERENCE**

AVV Dort No	Case	Case Capacitance	Rated Voltage [	DCL DF	ESR	100kHz RMS Current (mA)			*3	MOL		
AVX Part No.	Size	(μ <b>F</b> )	(V)	(μΑ)	@ 120Hz (%)	@ 100kHz (mΩ)	45°C	60°C	85°C	105°C	ΔC/C (%)	MSL
4 Volt												
F380G107MSALZT	S	100	4	80.0	10	200	474	332	_	237	*	3
6.3 Volt												
F380J105MUA	U	1	6.3	0.6	6	1500	100	-	70	50	*	3
F380J475MUA	U	4.7	6.3	20.0	10	1500	100	-	70	50	*	3
F380J106MMA	М	10	6.3	10.0	8	500	224	-	157	112	*	3
F380J106MMAAH1	М	10	6.3	10.0	8	300	289	-	202	144	*	3
F380J106MMAAH2	М	10	6.3	10.0	8	200	354	-	247	177	*	3
F380J106MSA	S	10	6.3	6.3	10	250	424	-	297	212	*	3
F380J106MUA	U	10	6.3	20.0	10	1500	100	-	70	50	*	3
F380J226MMA	М	22	6.3	13.9	10	500	224	-	157	112	*	3
F380J226MMAAH3	М	22	6.3	13.9	10	300	289	-	202	144	*	3
F380J226MMAAH1	М	22	6.3	13.9	10	200	354	-	247	177	*	3
F380J226MSA	S	22	6.3	13.9	10	200	474	-	332	237	*	3
F380J226MSAAH1	S	22	6.3	13.9	10	150	548	-	383	274	*	3
F380J336MMALZT	М	33	6.3	41.6	10	500	224	157	-	112	*	3
F380J336MSA	S	33	6.3	20.8	10	200	474	-	332	237	*	3
F380J476MMAAXE	М	47	6.3	59.2	10	500	224	157	-	112	*	3
F380J476MMAAXEH3	М	47	6.3	59.2	10	300	289	202	-	144	*	3
F380J476MSA	S	47	6.3	29.6	10	200	474	-	332	237	*	3
F380J476MSAAH1	S	47	6.3	29.6	10	150	548	-	383	274	*	3
F380J686MSALZT	S	68	6.3	86.0	10	200	474	332	-	237	*	3
F380J107MSALZT	S	100	6.3	126.0	10	200	474	332	-	237	*	3
F380J107MSALZTH1	S	100	6.3	126.0	10	150	548	383	-	274	*	3
					10 Volt							
F381A225MMA	M	2.2	10	10.0	6	500	224	-	157	112	*	3
F381A475MMA	М	4.7	10	10.0	6	500	224	-	157	112	*	3
F381A475MSA	S	4.7	10	4.7	10	300	387	_	271	194	*	3
F381A106MMA	М	10	10	10.0	15	500	224	-	157	112	*	3
F381A106MMAAH1	М	10	10	10.0	15	300	289	-	202	144	*	3
F381A226MMAAXE	М	22	10	44.0	10	500	224	157	-	112	*	3
F381A226MSA	S	22	10	22.0	10	200	474	-	332	237	*	3
F381A336MSALZT	S	33	10	99.0	10	200	474	332	-	237	*	3
F381A476MSALZT	S	47	10	94.0	10	200	474	332	_	237	*	3
25 Volt												
F381E225MMA	М	2.2	25	10.0	10	500	224	-	157	112	*	3
F381E475MSA	S	4.7	25	11.8	10	500	300	-	210	150	*	3

<sup>\*3: \( \</sup>Delta C/C Marked "\*"

230

Moisture Sensitivity Level (MSL) is defined according to J-STD-020

Item	All Case (%)
Damp Heat, steady state	-20 to +30
Rapid change of temperature	±20
Resistance soldering heat	±20
Surge	±20
Endurance	±20

Released ratings, (Low ESR)

\*4 (AXE) Rated temperature 60°C and H dimension 1.0mm Max. Please contact AVX when you need detail spec.


<sup>\*\* (</sup>LZT) Rated temperature 60°C. Please contact AVX when you need detail spec.




# **Conductive Polymer, Miniature, Undertab Solid Electrolytic Chip Capacitors**

## RECOMMENDED DEREATING FACTOR

Voltage and temperature derating as percentge of Vr





## **QUALIFICATION TABLE**

TEST	F38 series (Temperature Range -55°C to +105°C)	
IESI	Condition	
Damp Heat (Steady State)	At 40°C, 90 to 95% R.H., 500 hours (No voltage applied) Capacitance Change	
Temperature Cycles	At -55°C / +105°C, 30 minutes each, 5 cycles Capacitance Change	
Resistance to Soldering Heat	5 seconds reflow at 260°C Capacitance Change	
Surge	After application of surge voltage in series with a $1k\Omega$ resistor at the rate of 30 seconds ON, 30 seconds OFF, for $1000$ successive test cycles at $85^{\circ}C$ or $+60^{\circ}C$ ( $^{\circ}2$ ), capacitors shall meet the characteristic requirements in the table at Capacitance Change	oove.
Endurance	After 1000 hours' application of rated voltage in series with a 3Ω resistor at 85°C or +60°C (*2), capacitors shall meet the characteristic requirements in the table above. Capacitance Change	
Shear Test	After applying the pressure load of 5N for 10±1 seconds horizontally to the center of capacitor side body which has no electrode and has been soldered beforehand on a substrate, there shall be found neither exfoliation nor its sign at the terminal electrode.	5N (0.51kg · f) For 10±1 seconds
Terminal Strength	Keeping a capacitor surface-mounted on a substrate upside down and supporting the substrate at both of the opposite bottom points 45mm apart from the center of capacitor, the pressure strength is applied with a specified jig at the center of substrate so that the substrate may bend by 1mm as illustrated. Then, there shall be found no remarkable abnormality on the capacitor terminals.	R230 20mm 45mm 45mm


<sup>\*2</sup> LZT and AXE: Rated temperature +60°C, Surge and Endurance test temperature +60°C

NOTICE: DESIGN, SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.





#### SOLID ELECTROLYTIC CAPACITOR ROADMAP



## **FIVE CAPACITOR CONSTRUCTION STYLES**

