



an INFINIT® brand

Level Transmitter, 0-5mH2O/OIL 4-20mA out, 11-28V, Stainless 304, 10m Polyethylene



## LT989W Series IOT Pressure Sensors Technical Data Sheet

LT989W-5M10V1E22

### Features

- Level range 0-5 meters
- Sensor housing IP68
- Isolated construction, enable to measure various media
- Stainless steel

### Applications

- Industrial process control
- Liquid level measurement
- Chemical industries
- Water and Waste Management
- Mining

### Description

LT989W-5M10V1E22 is a highly stable, reliable and fully sealed submersible level transmitter. LT989W-5M10V1E22 level transmitter comes in a compact size, and is lightweight and stable. It can be used to measure liquid levels for many applications in metallurgy, mining, chemicals, water supply and waste management.

### Product Configuration

Application: Level Transmitter  
 Pressure Type: Gauge

### General Specifications

Description	Minimum	Typical	Maximum	Unit
Level Range	0		5	mH2O/OIL
Accuracy		±0.5		%Full Scale
Zero Thermal Error per °C		±0.05		% Full Scale/°C
Span Thermal Error per °C		±0.05		% Full Scale/°C
Long Term Stability		±20		mmH2O/year
Overpressure		1.5		xFull Scale

### Electrical Specifications

Description	Minimum	Typical	Maximum	Unit
Output Signal		4-20mA		
Power Supply/Excitation Level	11	24	28	VDC

### Material Specifications

Description	Material
Diaphragm	Stainless Steel 316L
Plug Housing	Stainless Steel 304
Tubing	NBR



an INFINIT® brand

Level Transmitter, 0-5mH2O/OIL 4-20mA out, 11-28V, Stainless 304, 10m Polyethylene



## LT989W Series IOT Pressure Sensors Technical Data Sheet

**LT989W-5M10V1E22**

O-Ring

Viton

### Mechanical Specifications

#### Electrical Connection

Wire Color	2-Wire
Black	+V
Red	0V/+OUT
White	GND

### Environmental Specifications

Temperature (Operating)	-10°C to 70°C
Temperature (Storage)	-20°C to 85°C
Certifications	ROHS Compliant
	CE Compliant


The Infinite Electronics portfolio includes coaxial cable assemblies, connectors, adapters and custom products, as well as our wireless product line which includes antennas, RF amplifiers, lightning and surge protectors, and NEMA rated enclosures.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

# LT989W-5M10V1E22 CAD Drawing

Level Transmitter, 0-5mH<sub>2</sub>O/OIL 4-20mA out, 11-28V, Stainless 304, 10m Polyethylene

REV	DESCRIPTION	DATE	APPROVED
1	INITIAL RELEASE	05/24/19	TOA



UNLESS OTHERWISE SPECIFIED LENGTH DIMENSIONS ARE IN INCHES DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS TOLERANCES: .X±.2 [5.08] FRACTIONS ± 1/32 .XX±.01 [25] ANGLES ± 1° .XXX±.005 [13] ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. THIRD-ANGLE PROJECTION		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM. ALL RIGHTS RESERVED.
		SHEET 1 OF 1 SCALE N/A
www.L-com.com   e-mail: CustomerService@L-com.com		DRAWN BY DZINN PART NUMBER LT989W-5M10V1E22
SIZE A CAGE 43321	DRAWN BY DZINN PART NUMBER LT989W-5M10V1E22	REV A

UNLESS OTHERWISE SPECIFIED LENGTH DIMENSIONS ARE IN INCHES DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS TOLERANCES: .X±.2 [5.08] FRACTIONS ± 1/32 .XX±.01 [25] ANGLES ± 1° .XXX±.005 [13] ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. THIRD-ANGLE PROJECTION

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.