



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**

Housing Type: **Tab Housing**

Number of Positions: **4**

Terminal Orientation: **Straight**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Style Code	C
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Housing Color	Natural
Mating Retention	With
Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Terminal Orientation	Straight



Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Locking Lance
Mounting Style	Panel Mount

Housing Features

Housing Material	Polyamide
------------------	-----------

Dimensions

Length	30.5 mm[1.2 in]
Centerline	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	200
--------------------	-----

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Also in the Series | RAST 5 IDC Connectors




Automotive, Truck, Bus, & Off-Road Terminals(8)



Connector Contacts(12)



Crimp Terminal Housings(41)



PCB Connector Mounting(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(4)




Standard Rectangular Connectors(108)



Wire-to-Board Connector Assemblies & Housings(214)



Wire-to-Board Connector Contacts(1)



Wire-to-Board Headers & Receptacles (459)

Customers Also Bought



TE Model / Part #9-927742-3
FASTIN FASTON HOUSING 3POS



TE Model / Part #1534077-3
MULTIFIT MK2ASSY 3P,IR



TE Model / Part #927742-6
6 POS FASTIN/ON HOUSING PANEL MOUNT



TE Model / Part #1241964-7
STD TIM HOUSING 7P




TE Model / Part #4-1534415-3
DUOPL POW FEM CON 3P



TE Model / Part #2-1241961-8
STD TIM HOUSING MKII 3POS



TE Model / Part #1-1241964-1
11POS STANDARD TIMER HOUSING



TE Model / Part #1534075-4
MULTIF.ASSY MK2 4P



TE Model / Part #1-1241961-8
STD TIM HOUSING MKII 3POS



TE Model / Part #1394355-2
MULTIFIT MK2ST-ST2P

Documents

Product Drawings

4POS FASTIN FASTON HOUSING

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_9-927742-4_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-927742-4_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-927742-4_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[FASTIN_FASTON_Product_Line](#)

English

[Product Specifications](#)

[QUALIFICATION TEST REPORT FOR 2-12 POS. FASTIN-FASTON* TAB HSG, RAST 5, PANEL MOUNT.](#)

English

English

[Product Environmental Compliance](#)

[MD_9-927742-4_06062015410_dmtec](#)

English

[MD_9-927742-4_06062015410_dmtec](#)

English

[Agency Approvals](#)

[VDE Certificate](#)

English