



an INFINIT® brand

Level Transmitter, 0-15mH2O/OIL 0.5-4.5V out, Stainless 304, 20m Polyethylene



## LT989W Series IOT Pressure Sensors Technical Data Sheet

LT989W-15M20V6K22

### Features

- Level range 0-15 meters
- Sensor housing IP68
- Isolated construction, enable to measure various media
- Stainless steel

### Applications

- Industrial process control
- Liquid level measurement
- Chemical industries
- Water and Waste Management
- Mining

### Description

LT989W-15M20V6K22 is a highly stable, reliable and fully sealed submersible level transmitter. LT989W-15M20V6K22 level transmitter comes in a compact size, and is lightweight and stable. It can be used to measure liquid levels for many applications in metallurgy, mining, chemicals, water supply and waste management.

### Product Configuration

Application: Level Transmitter  
 Pressure Type: Gauge

### General Specifications

Description	Minimum	Typical	Maximum	Unit
Level Range	0		15	mH2O/OIL
Accuracy		±0.5		%Full Scale
Zero Thermal Error		±0.02		% Full Scale/°C
Span Thermal Error		±0.05		% Full Scale/°C
Long Term Stability		±0.2		%Full Scale/year
Overpressure		1.5		xFull Scale

### Electrical Specifications

Description	Minimum	Typical	Maximum	Unit
Output Signal		0.5-4.5V		
Power Supply/Excitation Level		5		VDC
Output Load	10,000			Ohms

### Material Specifications

Description	Material
Diaphragm	Stainless Steel 316L
Plug Housing	Stainless Steel 304



an INFINIT® brand

Level Transmitter, 0-15mH2O/OIL 0.5-4.5V out, Stainless 304, 20m Polyethylene



## LT989W Series IOT Pressure Sensors Technical Data Sheet

LT989W-15M20V6K22

Tubing	NBR
O-Ring	Viton

### Mechanical Specifications

#### Electrical Connection

Wire Color	3-Wire
Black	+V
Red	+OUT
White	GND

### Environmental Specifications

Temperature (Operating)	-10°C to 70°C
Temperature (Storage)	-20°C to 85°C
Certifications	ROHS Compliant CE Compliant


The Infinite Electronics portfolio includes coaxial cable assemblies, connectors, adapters and custom products, as well as our wireless product line which includes antennas, RF amplifiers, lightning and surge protectors, and NEMA rated enclosures.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

# LT989W-15M20V6K22 CAD Drawing

Level Transmitter, 0-15mH<sub>2</sub>O/OIL 0.5-4.5V out, Stainless 304, 20m Polyethylene

REV		REVISIONS		DATE		APPROVED	
DESCRIPTION							
A	INITIAL RELEASE			05/24/19			TOA



UNLESS OTHERWISE SPECIFIED LENGTH DIMENSIONS ARE IN INCHES DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS		L-com an INFINITI® brand 50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA Phone: 1 800 341 5266   1 978 682 6936 Fax: 1 978 689 9484 www.L-com.com   e-mail: CustomerService@L-com.com		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM. ALL RIGHTS RESERVED.	
TOLERANCES: .X±.2 [5.08] FRACTIONS .XX±.01 [25] ± 1/32 XXX±.005 [13] ANGLES ± 1°		www.L-com.com   e-mail: CustomerService@L-com.com		SHEET 1 OF 1	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		SCALE N/A		REV A	
THIRD-ANGLE PROJECTION		SIZE [CAGE] A 43321		PART NUMBER LT989W-15M20V6K22	
DRAWN BY DZINN		DRAWN BY DZINN		REV A	

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T1Rev.B