


**Hochspannungstastkopf / High Voltage Probe**

TT-HVP 40AC



|                              |                                                                                    |
|------------------------------|------------------------------------------------------------------------------------|
| Model                        | TT-HVP 40AC                                                                        |
| Bestellnummer<br>Ordernummer | 15001                                                                              |
| Input Impedance              | 1000 M $\Omega$                                                                    |
| Division Ratio               | 1000:1                                                                             |
| Bandwidth                    | 300 Hz                                                                             |
| For use with                 | DMM<br>10 M $\Omega$ Imp.                                                          |
| Max. Test Voltage            | DC: 0-40 kV<br>AC: 1-28 kV<br>(50/60 Hz)                                           |
| Accuracy                     | DC $\pm$ 1% to 20kV<br>$\pm$ 2% to 40kV<br>AC $\pm$ 2% to 15kV<br>$\pm$ 3% to 28kV |
| Temperature Coefficient      | $\leq$ 200ppm/ $^{\circ}$ C                                                        |
| Operating Temperature        | 0 to 50 $^{\circ}$ C                                                               |
| Ground lead length           | 90 cm                                                                              |
| Cable length                 | 100 cm                                                                             |
| Connector                    | 4mm Plug                                                                           |
| Safety application           | IEC 1010 CAT II Pollution Degree2 / UL3111-1 / TÜV GS                              |



© TESTEC Elektronik GmbH – Bornheimer Landstr. 32-34 – D-60316 Frankfurt am Main

Tel.: +49-69-943335-0  
Fax: +49-69-943335-55