

Silicone-A Adhesive Sealants multicomp^{PRO}

RoHS
Compliant



MP004383

MP004384

MP004385

MP004386

MP004387

Acetate cross-linking fungicidal

Silicone A adhesive and sealant contains no solvents, has acetate-crosslinking properties, is strong, permanently elastic, resistant to ageing and chemicals, temperature resistant up to +180°C (+356°F), extremely elastic (breaking elongation >700%) and can be used universally. Silicone A adheres very well to steel, aluminium, glass, ceramics, and many additional materials.

Silicone A can be used in machine and system construction, ventilation and air conditioning systems, in the energy and electrical industry, in exhibition construction and shopfitting and in many additional industrial applications.

Technical Data

| | |
|---|--|
| Composition | : 1 Component - Polysiloxane (Acetate) |
| Density | : 1.03 g/cm ³ |
| Viscosity adhesive | : Pasty |
| Viscosity 0,5 (1/s)* | : 4210 Pa·s |
| Viscosity 50 (1/s)* | : 110 Pa·s |
| Stability/Run-off (ASTM D 222) | : 1 mm |
| Processing temperature | : +5°C to +35°C |
| Cure type | : By humidity |
| Curing condition | : +5°C to +40°C and 30% to 95% rel. humidity |
| Skin-overtime* | : 15 min. |
| Curing speed (first 24h) | : 2mm to 3mm |
| Volume change (DIN 52451) | : < -6 % |
| Gap filling up to max. | : 5 mm |
| Gap width up to max. | : 25 mm |
| Shelf life (+5°C to +25°C / +41°F to +77°F) | : 15 months |
| Shore A hardness (DIN 5355 / ASTM D 224) ± 5 | : 20 |
| Elongation at break acc. to ISO 37, S3A | : 700 % |
| Tensile strength acc. to ISO 37, S3A | : 1.4 N/mm ² |
| Tension strength value at 100 % (ISO 37, S3A) | : 0.3 N/mm ² |
| Movement capacity max. | : 25 % |
| Overpaintable (liquid paint) | : No |
| Building material category (DIN 412) | : B 2 |
| Temperature resistance | : -40°C to +180°C |

*Measured at 50% relative air humidity and +23°C

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp^{PRO}

Silicone-A Adhesive Sealants **multicomp**PRO

Surface pre-treatment

The surfaces must be clean and free of grease. Many surface contaminants, e.g. oil, dust and dirt, can be removed with Surface Cleaner. For heavily soiled metal surfaces, we recommend Cleaner Spray S; Sealant and Adhesive Remover is suitable for removing old paint or adhesive residues. Most materials can be bonded well to themselves and among each other. For certain materials or extreme requirements, we recommend the use of an adhesion agent (primer). Detailed information on this subject is contained in the primer selection table. A mechanical surface pre-treatment, e.g. sanding or sandblasting, can considerably improve the adhesion.

Processing

Processing cartridge

Application methods: Hand cartridge gun for 310 ml cartridges, compressed air gun (we recommend a variation with piston rod), automatic dosing systems.

Processing tube

Squeeze out by hand, close tube again immediately after use, opened tubes should be used up as quickly as possible.

Safety and health

When using products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets must be observed.

Joining the parts to be bonded

To ensure optimum wetting, the parts must be joined before the first skin has been formed on the adhesive (skin-over time).

Storage

When unopened and stored at room temperature (+23°C and 50 % rel. humidity), elastic one-component adhesives and sealants have a shelf life of 15 months.

Part Number Table

| Description | Part Number |
|---|-------------|
| Silicone Adhesive Sealant, Transparent, 310ml | MP004383 |
| Silicone Adhesive Sealant, White, 310ml | MP004384 |
| Silicone Adhesive Sealant, Grey, 310ml | MP004385 |
| Silicone Adhesive Sealant, Black, 310ml | MP004386 |
| Silicone Adhesive Sealant, Transparent, 85ml | MP004387 |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO