

Cisco-Compatible SFP-25G-SR-S SFP28 Transceiver - 25GBase-SR, Multimode LC, 850 nm, 328 ft. (100 m)

MODEL NUMBER: N286-25G-SR-S



Links a multimode Gigabit Ethernet network cable to a Cisco switch or server's SFP28 port.

Features

SFP28 Transceiver Designed for Connection to Your Cisco Network Switch or Server

This SFP28 transceiver allows you to connect a multimode fiber optic cable to a 25 Gbps network router, server or switch. It transmits data up to 328 feet (100 meters) using an 850 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

Functionally Equivalent to Cisco SFP-25G-SR-S Transceiver Module

The MSA-compliant N286-25G-SR-S functions just like the equivalent Cisco SFP-25G-SR-S transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the SFP-25G-SR-S.

Hot-Swappable for Installation Without Network Interruption

This input/output device is fully hot-swappable, so you can install it without a potentially costly 25 Gbps network shutdown or device reboot. Just plug the SFP28 end of the transceiver into your Cisco network device. The other end has an LC duplex connector to link with multimode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

Highlights

- SFP28 transceiver module
100% compatible with Cisco's equivalent module
- Provides 25 Gbps throughput up to 328 ft. (100 m) via multimode fiber cabling
- LC duplex female connector supports 25GBase-SR signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Meets or exceeds MSA standards and works in all MSA-compliant platforms

Applications

- Install an additional LC duplex port on a Cisco router, server or switch for the purpose of connecting a multimode Gigabit Ethernet network cable

System Requirements

- Cisco or other compatible network router, server or switch

Package Includes

- N286-25G-SR-S Cisco-Compatible SFP-25G-SR-S SFP28 Transceiver

Specifications

OVERVIEW	
UPC Code	037332248466
Optical Mode	OM4



PHYSICAL	
Color	Silver
Unit Dimensions (hwd / cm)	0.85 x 1.34 x 5.66
Unit Dimensions (hwd / in.)	0.33 x 0.53 x 2.23
Unit Dimensions (hwd / mm)	8.5 x 13.4 x 56.6
ENVIRONMENTAL	
Operating Temperature Range	32 to 158F (0 to 70C)
Storage Temperature Range	-40 to 185F (-40 to 85C)
Relative Humidity	5% to 85%
COMMUNICATIONS	
Signal Range (ft.)	328
Signal Range (m)	100
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (FEMALE)
Side B - Connector 1	SFP28 (Male)
FEATURES & SPECIFICATIONS	
Driver Required	No
Technology	SFP+/QSFP+/QSFP28
Wavelength	850nm
Brand Compatibility	Cisco
Optical Port	LC
Transmission Distance	100 m
Multi-Source Agreement (MSA) Compliant	Yes
SPECIAL FEATURES	
Data Transfer Rate	25Gbps
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>