

USB-A to RJ45 Rollover Console Cable (M/M) - Cisco Compatible, 250 Kbps, 6 ft., Black

MODEL NUMBER: U009-006-RJ45-X



Rollover console cable connects your computer or laptop's USB-A port to a serial-based Cisco device with a console port.

Features

Ideal for IT Pros Who Need a Connection Between Computer and Cisco Console Device

This rollover cable is designed for consumers or IT professionals who want a reliable connection between their computer or laptop's USB-A port and a Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port. The cable works with both older and new Cisco models, supporting data transfer rates up to 250 Kbps.

Top-Quality Construction for Top-of-the-Line Performance

No extra software or external power is required to use this six-foot cable. Premium double shielding eliminates crosstalk and reduce EMI/RFI line noise that can disturb your electronics and inflict hardware damage or data loss. The U009-006-RJ45-X works with Windows, Mac and Linux operating systems.

Highlights

- Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem
- 6 ft. cable supports data transfer speeds up to 250 Kbps
- Double-shielded construction cuts crosstalk and EMI/RFI line noise
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Windows, Mac and Linux

Applications

- Program, reset or reboot a serial-based Cisco switch, firewall, router or modem through its console port

System Requirements

- Computer or laptop with USB-A port
- Serial-based Cisco device with console port

Package Includes

- U009-006-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 6 ft.

Specifications

OVERVIEW	
UPC Code	037332222107
INPUT	
Cable Length (ft.)	6



Cable Length (m)	1.83
Cable Length (in.)	72
Cable Length (cm)	183
PHYSICAL	
Cable Jacket Type	PVC
Cable Outer Diameter (OD)	5.5mm; 4.7mm +/- 0.15
Color	Black
Material of Construction	PVC, PE
Unit Packaging Type	Polybag
Unit Weight (kg)	0.09
Unit Weight (lbs.)	0.1984
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 104F (0 ~ 40C)
Storage Temperature Range	-4 ~ 140F (-20 ~ 60C)
Relative Humidity	0% ~ 90% RH (Non-Condensing)
CONNECTIONS	
Side A - Connector 1	(1) USB A (MALE)
Side B - Connector 1	(1) RJ45 (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 1.1 (up to 12 Mbps)
Driver Required	No
USB Power Delivery (PD) Charging Support	No
Technology	USB
CERTIFICATIONS	
Certifications	Tested to RoHS, REACH, CE, FCC
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty